


NOTES:

1. MATERIALS:

BUSHING - COPPER ALLOY, NICKEL PLATED
 INSULATING WASHERS - PHENOLIC & THERMOPLASTIC
 SPRINGS - SPECIAL COPPER ALLOY, SILVER PLATED
 BUSHING WASHER - COPPER ALLOY, NICKEL PLATED
 BUTTON - THERMOPLASTIC, SEE TABLE FOR COLOR
 BUTTON RETAINING RING - TINNED MUSIC WIRE
 HEX NUT - COPPER ALLOY, NICKEL PLATED
 WASHER - STEEL, NICKEL PLATED

2. KI63A WASHER AND KI63B HEX NUT SHIPPED UNASSEMBLED.

3. THIS PRODUCT IS RoHS COMPLIANT.



1-A CIRCUIT

PART NUMBER	BUTTON COLOR
951X	RED
961X	BLACK

CUSTOMER DRAWING



STAR SYMBOL DENOTES CRITICAL DIMENSION

UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES
 - TWO PLACE DECIMALS ± 0.01
 - THREE PLACE DECIMALS ± 0.005
 - ANGLES $\pm 1^\circ$
 - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.

- FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ± 0.002

- REMOVE ALL BURRS

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH	MATERIAL			
SPEC No.	SPEC No.			
FIRST USED ON		SCALE		
		3:1		
DATE DRAWN	BY	CHKD	APVD	Switchcraft®
08-Oct-13	TO	TO 10-8-13	TJK 10-8-13	
NAME				PART No.
I-A CIRCUIT				951X_961X
TINI-SWITCH, RoHS				REV
				A

REV	ECO NUMBER	DATE	BY	APVD
A	25209	11-23-05	TO	TJK
REVISIONS				

Pro/Engineer CAD File

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

951 951X 961X