



RECOMMENDED
PANEL CUT-OUT
SCALE 1:1

PART NUMBER	FLANGE FINISH
E11	NICKEL PLATED
E11B	BLACK CHROME

CUSTOMER DRAWING

NOTES:

1. MATERIALS:
FLANGE - ZINC, SEE TABLE FOR FINISH
JACK BUSHING - BRASS, NICKEL PLATED
HEX NUT & WASHER - BRASS OR STEEL, NICKEL PLATED
2. ORIENTATION OF JACK IN FLANGE MAY VARY FROM SHOWN.
3. ADD A "PKG" SUFFIX TO THE PART NUMBER TO INCLUDE #4-40 MOUNTING SCREWS AND INDIVIDUAL PACKAGING.
4. THESE PRODUCTS ARE RoHS COMPLIANT.

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.																
					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	SIZE		WIDTH		MULT		LBS/M		TEMPER								
						FINISH SPEC No.						MATERIAL SPEC No.										
						FIRST USED ON				SCALE 1.5:1				Switchcraft®								
						DATE DRAWN 8/20/18		BY TJK	CHKD TJK 8/20/15		APVD TJK 8/20/15											
A	27565		9-3-15	TO		TJK	NAME #11 LITTEL JAX - Ø0.25 ON "E" SERIES MTG PLATE, RoHS										PART No. E11 SERIES				REV A	
REV	ECO NUMBER		DATE	BY		APVD																
REVISIONS					DO NOT SCALE DRAWING																	

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ±0.02 [0.5]
- THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[E11](#) [E11B](#) [E11PKG](#)