



WIRING

TIP - TIP

RING - RING

SLEEVE - SLEEVE

**LONG FRAME
MOLDED PLUG**

CABLE LENGTH

- 1 = 1 FOOT LONG
- 2 = 2 FEET LONG
- 3 = 3 FEET LONG
- 4 = 4 FEET LONG
- 5 = 5 FEET LONG
- 6 = 6 FEET LONG
- 7 = 7 FEET LONG
- 8 = 8 FEET LONG
- 9 = 9 FEET LONG
- 10 = 10 FEET LONG
- 11 = 11 FEET LONG
- 12 = 12 FEET LONG

X

RoHS COMPLIANT

CABLE JACKET COLOR

- BK = BLACK
- BL = BLUE
- GN = GREEN
- GY = GRAY
- O = ORANGE
- P = PURPLE
- R = RED
- Y = YELLOW

NOTES:

1. MATERIALS:

- PLUG - COPPER ALLOY, NICKEL PLATED
- INSULATORS - THERMOPLASTIC, BLACK
- OVERMOLD - THERMOPLASTIC, BLACK
- CABLE - 24 AWG, 110 OHM, PVC JACKET

2. THESE PRODUCTS ARE RoHS COMPLIANT.

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
					SIZE	WIDTH	MULT	LBS/M	TEMPER	
					UNLESS OTHERWISE SPECIFIED			FINISH		
					1. ALL DIMENSIONS IN INCHES [mm]			MATERIAL		
					- TWO PLACE DECIMALS ±0.02 [0.5]			SPEC No.		
					- THREE PLACE DECIMALS ±0.005 [0.13]			SCALE		
					FIRST USED ON		1:1			
B	28261	02/11/20	PC	TK	DATE DRAWN	BY	CHKD	APVD		
A	26228	4/3/07	TJK	TJK	2/10/12	TJK	TJK	2/10/12		
REV	ECO NUMBER	DATE	BY	APVD	NAME			PART No.	REV	
REVISIONS					DO NOT SCALE DRAWING			3 CONDUCTOR		SHEET 1 OF 1
					Ø0.25 LONGFRAME PATCHCORD			LF_X SERIES		
								B		

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[LF1BKX](#) [LF3BLX](#) [LF3RX](#) [LF5BL](#) [LF5GN](#) [LF5GY](#) [LF5O](#) [LF5R](#) [LF5Y](#) [LF1RX](#) [LF2GYX](#) [LF2YX](#) [LF4BLX](#) [LF4GNX](#)
[LF4RX](#) [LF10GNX](#)