







AS VIEWED FROM FRONT MATING VIEW



CUSTOMER DRAWING

NOTES:

1. MATERIALS:
HOUSING - COPPER ALLOY, NICKEL PLATED OR BLACK CHROME PLATED
LATCH - SPECIAL COPPER ALLOY, NICKEL PLATED
LATCH BUTTON - THERMOPLASTIC, BLACK
CONTACTS - COPPER ALLOY, SILVER PLATED OR GOLD PLATED
INSERT - THERMOPLASTIC, DARK BROWN OR BLACK
INSULATOR - THERMOPLASTIC, DARK BROWN
CABLE CLAMP - STEEL, ELECTRO-TIN PLATED
HANDLE - THERMOPLASTIC, BLACK, WHITE, OR NICKEL PLATED
FLEX RELIEF - THERMOPLASTIC, BLACK OR WHITE

2. THIS PRODUCT IS RoHS COMPLIANT.

G	27805	11-9-16	TO	TJK	UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
F	27788	10-13-16	PC	TJK		SIZE	WIDTH		MULT		LBS/M		TEMPER		
E	27486	04-20-15	PC	TJK		FINISH SPEC No.						MATERIAL SPEC No.			
D	26916	03-06-12	PC	TJK		FIRST USED ON				SCALE 2:1		Switchcraft®			
C	25955	09-22-08	JEB	TJK		DATE DRAWN	BY	CHKD		APVD					
						11-02-10	JEB	JEB		TJK					
H	27971	12/13/17	PC	TJK				11-02-10		03-08-11		SHEET 1 OF 1			
REV	ECO NUMBER	DATE	BY	APVD	DO NOT SCALE DRAWING	NAME TINI QG FEMALE STRAIGHT CORD PLUG, RoHS						PART No. TA_FX SERIES			REV H
REVISIONS															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[TA5FLWX](#)