



**NOTES:**

- ADAPTER MEETS:  
CAT5e: TIA/EIA-568-B.2 STANDARD  
CAT6: TIA/EIA-568-B.2-1 STANDARD  
D CAT6A: TIA/ANSI-568-C.2 STANDARD
- MATERIALS:  
RJ45 MOUNTING PLATE - THERMOPLASTIC, BLACK  
RJ45 HOUSING - THERMOPLASTIC, BLACK  
RJ45 SHIELD - COPPER ALLOY, NICKEL PLATED
- FOR SCREWS TO BE SHIPPED WITH ASSEMBLY, ADD SUFFIX -PKG TO PART NUMBER.
- WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-LBS MAXIMUM.
- THIS PRODUCT IS RoHS COMPLIANT.

**RECOMMENDED PANEL CUT-OUT**

PART NUMBER		RJ45 ADAPTER	
EHRJ45P5E		CAT5e UNSHIELDED	
EHRJ45P5ES		CAT5e SHIELDED	
EHRJ45P6		CAT6 UNSHIELDED	
EHRJ45P6S		CAT6 SHIELDED	
EHRJ45P6A		CAT6A UNSHIELDED	
EHRJ45P6AS		CAT6A SHIELDED	

**CUSTOMER DRAWING**

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH		MATERIAL		
SPEC No.		SPEC No.		
FIRST USED ON		SCALE		
DATE DRAWN		BY	CHKD	APVD
7/7/08	JGK	RS	TJK	
NAME		EH SERIES		PART No.
		RJ45 ADAPTER, RoHS		EHRJ45P SERIES
REV				D

**REVISIONS**

REV	ECO NUMBER	DATE	BY	APVD
D	27721	6-21-16	TO	TJK
C	27585	10/08/15	PC	TJK
B	27247	1/24/14	JGK	TJK
A	26387	5/15/09	RS	TJK

**DO NOT SCALE DRAWING**

**SolidWorks CAD File**

**Switchcraft®**

SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[EHRJ45P5ES](#) [EHRJ45P6AS](#) [EHRJ45P6A](#)