



### 913S/913DS MOMENTARY SWITCH

HOUSING - NICKEL PLATED COPPER ALLOY  
 BUTTON SEAL - THERMOPLASTIC, BLACK  
 INSULATORS - RIGID PLASTIC  
 TERMINALS - SILVER PLATED COPPER ALLOY  
 O-RING - THERMOPLASTIC RUBBER

### SEALING HANDLE

HANDLE - THERMOPLASTIC, BLACK  
 OVERMOLD - THERMOPLASTIC RUBBER, BLACK

### NOTES:

1. COMPLETED ASSEMBLY ON ACCEPTABLE CABLE SHALL MEET IP67 RATING.
2. OUTER JACKET OF CABLE USED IN ASSEMBLY MUST BE SMOOTH, ROUND, FLEXIBLE, AND FALL WITHIN THE SPECIFIED CABLE RANGE PER THE HANDLE.
3. USING CABLE OD CLOSER TO THE CABLE RANGE MAXIMUM PER HANDLE WILL ENSURE A MORE ROBUST SEAL.
4. BUTTON AND O-RING SHIPPED UNASSEMBLED.
5. THIS PART IS RoHS COMPLIANT.

**CUSTOMER DRAWING**

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.														
					UNLESS OTHERWISE SPECIFIED  1. ALL DIMENSIONS IN INCHES  - TWO PLACE DECIMALS     ±0.02  - THREE PLACE DECIMALS     ±0.005	SIZE		WIDTH		MULT		LBS/M		TEMPER						
0E	NOTES	02/19/15	TS	-		FINISH						MATERIAL								
0D	PART NUMBERS	01/22/15	TS	-		SPEC No.						SPEC No.								
0C	CABLE RANGES	05/13/14	TS	-		FIRST USED ON -				SCALE 1:1.5		Switchcraft®								
0B	CABLE DIAMETERS	08/02/13	TS	-		DATE DRAWN 05/30/12		BY TS	CHKD TS 05/30/12		APVD - -									
0A	INITIAL DRAWING	05/30/12	TS	-		NAME    SEALED CORD SWITCH ASSEMBLY, ROHS						PART No.    EP913 S    SERIES								
REV	ECO NUMBER	DATE	BY	APVD	DO NOT SCALE DRAWING						REV    0E									
REVISIONS																				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[EP913S14](#) [EP913S17](#) [EP913DS20](#) [EP913S20](#) [EP913S23](#) [EP913DS14](#) [EP913DS23](#) [EP913DS17](#)