



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

MATERIAL:

- 6 HOUSING: POLYCARBONATE (REF: LEXAN 500)  
BUSHING & MTG. HARDWARE: NICKEL PLATED BRASS  
SLEEVE & SHUNT TERMINALS: SILVER PLATED COPPER ALLOY  
TIP TERMINAL: SILVER PLATED BERYLCO 25

CUSTOMER DRAWING

CAD/CAM DWG. NO.  
s.mdpc2ara\_cd  
SHEET 1 OF 1

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION. SEE S/C ENGINEERING STANDARD ES-0001.					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSE ONLY.									
G	ECO #21788	6-24-97	RC	JF	UNLESS OTHERWISE SPECIFIED					SIZE		WIDTH		MULT		LBS./M		TEMPER	
F	ECO #20627	1-25-96	DEA	TAO	1. ALL DIMENSIONS IN INCHES TWO PLACE DECIMAL ±.01 THREE PLACE DECIMAL ±.005 FRACTIONAL DIMENSIONS ±1/64 ANGLES ±1/2° ALL DIA'S CONCENTRIC WITHIN .005 T.I.R. 2. REMOVE ALL BURRS 3. MAKE NO DIMENSIONAL ALLOWANCES FOR APPLIED FINISHES, I.E., PLATING, PAINTING, ETC. 4. HOLES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±.002					FINISH				MATERIAL					
E	ECO #20522	4-4-96	DEA	JF						SPEC. NO.				SPEC. NO.					
D	ECO #20358	2-11-95	DEA	TAO						FIRST USED ON				SCALE					
C	ECO #20212	2-11-95	DEA	TAO						DATE DRAWN				I = 0.100					
B	REDRAWN ON CAD ECO #20206	2-11-95	DEA	TAO						BY		CHK'D		APP'D		Switchcraft®			
										6-4-76		FGD		JRH 1-28-77					
ISSUE	CHANGE NO.		DATE		BY		APP'D		NAME		MICRO-JACK				PART NO.		ISSUE		
REVISIONS					DO NOT SCALE DRAWING									MDPC2ARA		G			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[MDPC2ARA](#)