



- NOTES:
- MATERIALS:
CHASIS, FRAME - CRS, BLACK EPOXY PAINT
TOP COVER - ALUMINUM, BLACK ANNOXIDIZED
JACK INSULATOR BLOCKS - THERMOPLASTIC, BLACK
JACK FRAME - CRS, NICKEL PLATED
JACK BUSHING - BRASS, NICKEL PLATED
 - MOUNTING SCREWS, DESIGNATION STRIPS, MARKING STRIPS AND COVERS SHIPPED UNASSEMBLED.
 - RoHS COMPLIANT.

PART NUMBER	TYPE	JACK PART NUMBERS
MT48K1FNX	FULL NORMAL	XMT334BNX (48)
MT48K1HNX	HALF NORMAL	XMT332BNX (24) TOP XMT334BNX (24) BOTTOM
MT48K1NNX	NON-NORMAL	XMT332BNX (48)
MT48K1NSX	FULL NORMAL NORMALS STRAPPED	XMT334BNX (48)

CUSTOMER DRAWING

					<div>★ STAR SYMBOL DENOTES CRITICAL DIMENSION</div> <div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.</div> <div>2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002</div> <div>3. REMOVE ALL BURRS</div> <div>DO NOT SCALE DRAWING</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE	WIDTH		MULT	LBS/M	TEMPER	
						FINISH SPEC No.				MATERIAL SPEC No.		
						FIRST USED ON			SCALE 1:2		<div>Switchcraft®</div> <div>SHEET OF </div>	
						DATE DRAWN 24-Nov-10	BY TO	CHKD TO 11-24-10	APVD TJK 11-24-10			
B	27743	7-25-16	TO	TJK	NAME IRU, UNWIRED					PART No. MT48KI_X-SERIES		REV B
A	26405	6-24-09	TO	TJK	P-KIT ASSEMBLY, RoHS							
REV	ECO NUMBER	DATE	BY	APVD								
REVISIONS												



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[MT48K3NSX](#)