





NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. SEE DRAWING HPMIMIX FOR HOLE PATTERN.
3. DIMENSIONS ARE FOR REFERENCE ONLY.




MATING FACE
ASSY: W7A81-8PG-3ES SHOWN




ASSEMBLED VIEW
ASSY: W7A81-8PG-3ES SHOWN



RECOMMENDED PANEL CUTOUT




ASSEMBLED VIEW
ASSY: W7A82-8PG-300 SHOWN



WIRING END
ASSY: W7A82-8PG-300 SHOWN

CONNECTOR P/N	POSITIONS		CONTACT STYLE	EPOXY
	#16	#26		
W7A80-8PG-300	2	6	CRIMP	(NONE)
W7A81-8PG-300			PC TAIL	(NONE)
W7A81-8PG-3ES			PC TAIL	ES
W7A82-8PG-300			SOLDER	(NONE)
W7A82-8PG-3ES			SOLDER	ES



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

PRELIMINARY

RoHS COMPLIANT

0A	PNK	10-29-14	PDR 14001 PRELIMINARY		
REV.	INIT.	DATE	DESCRIPTION		
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: PNK	DATE: 10-29-14	 601 E. WILDWOOD VILLA PARK, IL 60181
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			CHECKED BY:		
			APPROVED BY:		TITLE: PANEL-MOUNT CONNECTOR 2-16 + 6-26 PIN CONTACTS MINI-CON-X POWER/SIGNAL
			SCALE: NTS	SIZE: B	SHEET: 1 OF 1
			FILE: W7A8X-8PG-3XX_CD	DIRECTORY: SLW	PART NUMBER: W7A8X-8PG-3XX_CD
			CUSTOMER: STANDARD PRODUCT		
			REV 0A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[W7A80-8PG-300](#) [W7A81-8PG-3ES](#) [W7A81-8PG-300](#) [W7A82-8PG-3ES](#) [W7A82-8PG-300](#)