

FAKRA Code C Blue Connector

FAKRA Gen 2 – Code C for RG-174, RG-316, TGC/CFD-200, TGC-302/RTK031, TGC-1.5DS cables



Product description

Taoglas is a leading provider of advanced technology for a smarter world. Our solutions include advanced components and technologies and help OEMs, enterprises, and communities to resolve the complexities of bringing digital transformation solutions to market quickly and cost effectively. Focused on best-in-class, high-performance antenna and RF design with advanced positioning, imaging, audio and artificial intelligence technologies, Taoglas understands the importance of high-performance connections.

Taoglas GEN.2 FAKRA connectors utilize a metal SMB connector embedded within a plastic enclosure that is colour coded and keyed for ease of identification and assembly. They have been designed with a swivel style housing for ease of installation. They are designed for high-volume production, automated harness assembly and provide superior performance. They are manufactured with the highest precision and are thoroughly tested to meet USCAR-2 and USCAR-17 standards. All Taoglas connectors are RoHS & REACH compliant.

The Blue Code C connector is typically used for GNSS connections and is available in both for multiple cable diameters.

Features

- Optimized for automated manufacturing
- Full Series of colours available
- RF performance up to 6GHz
- Primary and Secondary Locks
- Tulip contact/ anti-stubbing
- Housing inner ring/ anti-scooping
- Fully compliant to USCAR requirements

Specifications


Electrical		
Impedance	50Ω Nominal	
Frequency Range	DC - 6000MHz	
VSWR (Return Loss)	0 ~ 3000MHz < 1.3	3000 ~ 6000MHz < 1.5
D.W.V	800 VRMS, Min	
Insulation Resistance	≥100MΩ	
Mechanical		
Durability	25 Cycles Min	
Insertion Force	≤25N	
Withdraw Force	≥2N	
Locking Device Strength	≥80N	
Outer Contact Rentention Force in Housing	≥100N	
Suitable Cables	RG-174, RG-316, TGC/CFD200, TGC-1.5DS	
Storage and Opeartional Tempeature Range	-40°C - 105°C	




FAKRA Code C - Blue

Mechanical Drawings


FK2FCDK - Code C Female Jack for RG-174/RG-316




FK2FCVV - Code C Female Jack for TGC-302/RTK031



FK2FCG - Code C Female Jack for TGC/CFD200



FK2FCF - Code C Female Jack for TGC-1.5DS



Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taoglas:](#)

[FK2FCF](#)