



NOTES:

1. MATERIALS:
CHASIS, FRAME - CRS, BLACK EPOXY PAINT
TOP COVER - ALUMINUM, BLACK ANNOXIDIZED
JACK INSULATOR BLOCKS - THERMOPLASTIC, BLACK
JACK FRAME - CRS, NICKEL PLATED
JACK BUSHING - BRASS, NICKEL PLATED
2. MOUNTING SCREWS, DESIGNATION STRIPS, MARKING STRIPS AND COVERS SHIPPED UNASSEMBLED.
3. RoHS COMPLIANT.

PART NUMBER	TYPE	JACK PART NUMBERS
MT48K1FNX	FULL NORMAL	XMT334BNX (48)
MT48K1HNX	HALF NORMAL	XMT332BNX (24) TOP XMT334BNX (24) BOTTOM
MT48K1NNX	NON-NORMAL	XMT332BNX (48)
MT48K1NSX	FULL NORMAL NORMALS STRAPPED	XMT334BNX (48)

CUSTOMER DRAWING

					<div>★ STAR SYMBOL DENOTES CRITICAL DIMENSION</div> <div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.</div> <div>2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002</div> <div>3. REMOVE ALL BURRS</div> <div>DO NOT SCALE DRAWING</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE	WIDTH		MULT	LBS/M	TEMPER	
						FINISH SPEC No.				MATERIAL SPEC No.		
						FIRST USED ON			SCALE 1:2		<div>Switchcraft®</div>	
						DATE DRAWN	BY	CHKD	APVD			
B	27743	7-25-16	TO	TJK		24-Nov-10	TO	11-24-10	TJK			
A	26405	6-24-09	TO	TJK								
REV	ECO NUMBER	DATE	BY	APVD		NAME				PART No.	REV	
REVISIONS						IRU, UNWIRED P-KIT ASSEMBLY, RoHS				MT48KI_X-SERIES	B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[MT48K1FNX](#) [MT48K1HNX](#) [MT48K1NNX](#) [MT48K1NSX](#) [MT48K3FNX](#) [MT48K3HNX](#) [MT48K3NNX](#)