

NOTES:

- 0.185 [3,7] MAX PANEL THICKNESS
- MATERIALS:
BODY - BRASS, NICKEL OR GOLD PLATED
INSULATOR - DELRIN
NUT - BRASS, NICKEL PLATED
WASHER - BRONZE, NICKEL PLATED
- THIS PRODUCT IS RoHS COMPLIANT.

BULKHEAD PHONO JACK


BPJ J 01 AU X RoHS COMPLIANT

JACK TO JACK

PLATING:
AU = GOLD
BLANK = NICKEL

INSULATOR COLOR

- 01 = BLACK
- 02 = RED
- 03 = WHITE
- 04 = YELLOW
- 05 = BLUE
- 06 = GREEN



CUSTOMER DRAWING



STAR SYMBOL DENOTES CRITICAL DIMENSION

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES
-TWO PLACE DECIMALS ± 0.01
-THREE PLACE DECIMALS ± 0.005
-ANGLES $\pm 1^\circ$
-ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.

- FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ± 0.002

- REMOVE ALL BURRS

DO NOT SCALE DRAWING

SIZE	WIDTH	MULT	LBS/M	TEMPER
------	-------	------	-------	--------

FINISH	MATERIAL
SPEC No.	SPEC No.

FIRST USED ON	SCALE
	1:1.66

DATE DRAWN	BY	CHKD	APVD
16-Mar-07	TJK	TJK	TJK

NAME	PART No.	REV
RCA BULKHEAD PHONO ADAPTOR JACK TO JACK, RoHS	BPJJ_X SERIES	A

Switchcraft®

SHEET 1 OF 1

REV	ECO NUMBER	DATE	BY	APVD
A	26014	3-16-07	TJK	TJK
REVISIONS				

Pro/Engineer CAD File

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[BPJJ06X](#) [BPJJ05X](#) [BPJJ06AUX](#) [BPJJ05AUX](#)