



Soldering Tips - Hakko Compatible

HS SERIES

COMPATIBLE STATIONS: Hakko FX-888, Hakko FX-888E, Hakko FX-8801, Hakko 926, Hakko 928, Hakko 936, Hakko 937, Hakko 951, Hakko 952, Hakko 958, Hakko 959, Hakko 701, Hakko 702B, Hakko 900M, Hakko 900M-ESD, Hakko 907, Hakko 907-ESD

Plato is one of the largest manufacturers of solder tips in the world, producing tips to fit all of the most popular solder stations. The long life and fast heat recovery of a Plato solder tip increases user effectiveness and decreases production times. All Plato solder tips manufactured since January 2004 are tinned with Lead-Free solder. Plato is the name for reliable soldering supplies.

Long Life: Using a high quality Plato solder tip increases solder speeds and decreases the total cost of manufacture. Higher temperatures and high tin content solders, common in lead-free solder processes, place additional strain on soldering iron tips. The long life of a Plato solder iron tip reduces tip changes, decreasing the total number of tips used and decreasing production time.

Rapid Heat Recovery: Plato solder tips are constructed from highly conductive premium grade copper to transmit heat to the work more quickly than other brands. This quick heat recovery enables more joints to be soldered per minute, thus reducing manufacturing time and costs.




- HS - Popular Plato tip shapes
- HS18 - New tip designs for faster heat recovery
- Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- Fewer tip change overs

[Request More Info](#)

Product Dimensions


HS-5701 Bevel, micro

Cross Reference: Hakko 900M-T-1C, Hakko T18-C1
1.2mm
10 units/case



HS-5702 Bevel, micro

Cross Reference: Hakko 900M-T-2C, Hakko T18-C2
2.0mm
10 units/case




HS-5703 Bevel

Cross Reference: Hakko 900M-T-3C, Hakko T18-C3
3.0mm
10 units/case



HS-5875 Bevel

Cross Reference: Hakko 900M-T-4C, Hakko T18-C4
4.0mm
10 units/case






HS-2863 Screwdriver

Cross Reference: Hakko 900M-T-0.8D, Hakko T18-D08
0.8mm
10 units/case



HS-2751 Screwdriver

Cross Reference: Hakko 900M-T-1.6D, Hakko T18-D16
1.6mm
10 units/case



HS-2753 Screwdriver

Cross Reference: Hakko 900M-T-3.2D, Hakko T18-D32
3.2mm
10 units/case




HS-4791 Angled SMD

Cross Reference: Hakko 900M-T-0.2RB, Hakko T18-BR02
0.4mm
10 units/case




HS-0925 Angled SMD

Cross Reference: Hakko 900M-T-H
1.6mm
10 units/case



HS-4785 Point, rounded

Cross Reference: Hakko 900M-T-B, Hakko T18-B
1.0mm x 6.4mm tin length
10 units/case



HS-4786 Point, rounded

Cross Reference: Hakko 900M-T-LB, Hakko T18-BL
0.8mm
10 units/case



HS-4787 Point, micro rounded


Cross Reference: Hakko 900M-T-I, Hakko T18-I
0.4mm
10 units/case





HS-0927 Knife

Cross Reference: Hakko 900M-T-K, Hakko T18-K
6.3mm
10 units/case




HS-2796 Screwdriver

Cross Reference: Hakko 900M-T-1.2D, Hakko T18-D12
1.2mm
10 units/case



HS-1665 Screwdriver

Cross Reference: Hakko 900M-T-S3, Hakko T18-S3
5.2mm
10 units/case



HS-8157 Angled SMD

Cross Reference: Hakko 900M-T-S5, Hakko T18-S5
0.4mm
10 units/case



HS-0530 SMD flow tip

Cross Reference: Hakko SMD Flow Tip
3.3mm
10 units/case



HS-0531 SMD flow tip

3.4mm
10 units/case



North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2017 Illinois Tool Works

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Plato:

[HS-0925](#) [HS-0927](#) [HS-4785](#) [HS-4791](#) [HS-5702](#) [HS-6030](#) [HS-8175](#) [HS-8179](#)

Techspray:

[HS-0530](#) [HS-0531](#) [HS-1665](#) [HS-2751](#) [HS-2752](#) [HS-2753](#) [HS-2796](#) [HS-2863](#) [HS-4786](#) [HS-4787](#) [HS-4988](#) [HS-5701](#) [HS-5703](#) [HS-5875](#) [HS-8157](#)