



Technical Data Sheet

Rev. A (8/17) Page 1 of 2


Soldering Tips

Compatible with ¼" Hexacon, American Beauty and Esico Irons

Compatible Stations: Hexacon – ¼" tip, American Beauty – ¼" tip, Esico – ¼" tip

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times.


- Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- Fewer tip change overs



Product Dimensions


42-347 Screwdriver – 2.4mm

Cross Reference: American Beauty 714, Esico 422-144, Esico 422-347, Hexacon HT358
10 units/bag



42-355 Screwdriver – 1.6mm

Cross Reference: American Beauty 716, Esico 422-108, Esico 422-132, Hexacon HT 359
10 units/bag




44-152 Screwdriver – 6.4mm

Cross Reference: American Beauty 704, Esico 410-126, Esico 410-140, Hexacon HT553
10 units/bag




44-352 Chisel – 4.8mm

Cross Reference: American Beauty 715, Hexacon HT313, Hexacon HT202
10 units/bag




44-386 Screwdriver – 4.0mm

10 units/bag



44-390 Screwdriver – 3.2mm

Cross Reference: American Beauty 721, Esico 420-106, Esico 420-119, Hexacon HT417
10 units/bag




Soldering Tips

Compatible with 1/4" Hexacon, American Beauty and Esico Irons


44-715 Screwdriver, long – 3.2mm

Cross Reference: Esico 420-114, Hexacon HT426
10 units/bag



46-626 Screwdriver – 4.8mm

Cross Reference: Esico 426-161, Esico 425-173,
Hexacon HT552
10 units/bag



Environmental Policy

We are committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Plato products are supported by global sales, technical and customer services resources.

For additional technical information on these products or other Plato products in the United States, call the technical sales department at 800-858-4043, email info@plato products.com or visit our web site at: www.platoproducts.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Our only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will we be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

North America

ITW Contamination Control - Electronics
8125 Cobb Center Drive
Kennesaw, GA 30152
800-858-4043
info@plato products.com

Europe

ITW Contamination Control BV
Saffierlaan 5, 2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
info@itw-cc.com

Countries outside the US

Call to locate a distributor in your country

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Plato:

[42-347](#) [44-152](#) [44-352](#) [44-386](#) [44-390](#) [44-715](#) [46-626](#)

Techspray:

[42-355](#)