


Soldering Tips – 3/8”

Compatible Stations: Hexacon – 3/8” tip, American Beauty – 3/8” tip, Esico – 3/8” tip

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times.

- **Fast heat recovering increases soldering speed**
- **Longer tip reduces manufacturing costs**
- **Fewer tip change-overs**



Product Dimensions

66-145 Chisel

Cross Reference: Hexacon HT151
9.5mm
10 units/case



66-201 Square

Cross Reference: American Beauty 43D, Hexacon HT566
1.6mm
10 units/case




66-300 Screwdriver

Cross Reference: American Beauty 823, Hexacon HT449
6.4mm
10 units/case



66-349 Screwdriver

Cross Reference: Hexacon HT470
8.0mm
10 units/case




Soldering Tips – 3/8"

Product Dimensions

66-367 Screwdriver

Cross Reference: Hexacon 66-367, Hexacon HT129
4.8mm
10 units/case



66-409 Conical

Cross Reference: N/A
1.6mm
10 units/case




66-627 Screwdriver

Cross Reference: N/A
4.8mm
10 units/case



66-704 Chisel

Cross Reference: American Beauty 43C
9.5mm
10 units/case



Environmental Policy

We are committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Plato products are supported by global sales, technical and customer services resources.

For additional technical information on these products or other Plato products in the United States, call the technical sales department at 800-858-4043, email info@platoproducts.com or visit our web site at: www.platoproducts.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Our only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will we be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



● North America

ITW Contamination Control - Electronics
8125 Cobb Center Drive
Kennesaw, GA 30152
800-858-4043
info@platoproducts.com

● Europe

ITW Contamination Control BV
Saffierlaan 5, 2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
info@itw-cc.com

● Countries outside the US

Call to locate a distributor in your country

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Plato:

[66-145](#) [66-201](#) [66-300](#) [66-349](#) [66-367](#) [66-409](#) [66-627](#) [66-704](#)