

Technical Data Sheet

Rev. B (12/21) Page 1 of 3

Soldering Tips - Hakko CompatibleHS SERIES

Compatible Stations: Hakko FX-888, Hakko FX-888D, Hakko FX-889, Hakko FR-701, Hakko FR-702, Hakko 926, Hakko 928, Hakko 936, Hakko 937, Hakko 951, Hakko 952, Hakko 958, Hakko 959, Hakko 701, Hakko 702, Hakko FX-8801, Hakko FX-8802, Hakko FX-8803, Hakko FX-600, Hakko 900M, Hakko 900M-ESD, Hakko 907, Hakko 907-ESD, Hakko 913

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times.




- Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- Fewer tip change overs

Product Dimensions

HS-0530 SMD Flow Tip

Cross Reference: Hakko SMD Flow Tip 3.3mm


10 units/bag



HS-0925 Angled SMD

Cross Reference: Hakko 900M-T-H

1.6mm 10 units/bag



HS-1665 Screwdriver

Cross Reference: Hakko 900M-T-S3, Hakko T18-S3 5.2mm


10 units/bag



HS-0531 SMD Flow Tip

Cross Reference: NA

3.4mm




HS-0927 Knife

Cross Reference: Hakko 900M-T-K, Hakko T18-K

6.3mm

10 units/bag



HS-2751 Screwdriver

Cross Reference: Hakko 900M-T-1.6D, Hakko T18-D16

1.6mm

10 units/bag





Rev. B (12/21) Page 2 of 3

Soldering Tips - Hakko Compatible

HS SERIES

Product Dimensions

HS-2753 Screwdriver

Cross Reference: Hakko 900M-T-3.2D, Hakko T18-D32 10 units/bag



HS-2863 Screwdriver

Cross Reference: Hakko 900M-T-0.8D, Hakko T18-D08 0.8mm





HS-4786 Point, rounded

Cross Reference: Hakko 900N-T-LB, Hakko T18-BL 0.8mm 10 units/bag



HS-4791 Angled SMD

Cross Reference: Hakko 900M-T-0.2RB, Hakko T18-BR02 0.4mm



HS-5701 Bevel, micro

Cross Reference: Hakko 900M-T-1C, Hakko T18-C1 1.2mm



HS-5703 Bevel

Cross Reference: Hakko 900M-T-#C, Hakko T18-C3




HS-2796 Screwdriver

Cross Reference: Hakko 900T-1.2D, Hakko T18-D12 1.2mm 10 units/bag



HS-4785 Point, rounded

Cross Reference: Hakko 900M-T-B, Hakko T18-B 1.0mm x 6.4mm tin length 10 units/bag



HS-4787 Point, micro rounded

Cross Reference: Hakko 900M-T-I, Hakko T18-I 0.4mm 10 units/bag



HS-4988 Point, micro

Cross Reference: Hakko 900M-T-SB, T18-SB 0.2mm 10 units/bag



HS-5702 Bevel, micro

Cross Reference: Hakko 900M-T-2C, Hakko T18-C2 2.0mm 10 units/baq

5/64" (2.0) T

HS-5875 Bevel

Cross Reference: Hakko 900M-T-4C, Hakko T18-C4 4.9mm





Rev. B (12/21) Page 3 of 3

Soldering Tips - Hakko Compatible

HS SERIES

Product Dimensions

HS-8157 Angled SMD

Cross Reference: Hakko 900M-T-S5, Hakko T18-S5 0.4mm





Environmental Policy

We are committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Plato products are supported by global sales, technical and customer services resources.

For additional technical information on these products or other Plato products in the United States, call the technical sales department at 800-858-4043, email info@platoproducts.com or visit our web site at: www.platoproducts.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Our only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will we be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Plato:

HS-0925 HS-0927 HS-4785 HS-4791 HS-5702

Techspray:

<u>HS-0530</u> <u>HS-0531</u> <u>HS-1665</u> <u>HS-2751</u> <u>HS-2753</u> <u>HS-2796</u> <u>HS-2863</u> <u>HS-4786</u> <u>HS-4787</u> <u>HS-5701</u> <u>HS-5703</u> <u>HS-5703</u> <u>HS-5705</u>