



APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/8/20	
A		UPDATE DRAWING	11/4/20	LH/JL



OPLD2BNNC1NA	PEI Aquatic Blue	W/O
OPLD2BNNC1PA	PEI Aquatic Blue	W/
OPLC2BNNC1NA	PBT Beige 7501U	W/O
OPLA2BNNC1NA	PBT Green 7737C	W/O
OPLC2BNNC1PA	PBT Beige 7501U	W/
OPLA2BNNC1PA	PBT Green 7737C	W/
OPLB2BNNC1NA	PEI Blue 2184C	W/O
OPLB2BNNC1PA	PEI Blue 2184C	W/
Part name	Material, Color	EMI

#### SPECIFICATIONS:

Material:

Housing: See Chart, rated UL 94V-0, Color: See Chart

Cap: PP, rated UL 94V-0, Color: White

Spring: SUS

Sleeve: Zirconia Ceramic

Electrical:

Standards of IEC 61754-20, YD/T 1272.1-2003

Repeatability: 1000 min times

Insertion loss: 0.2dB max

Interchangeability: 0.2dB

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE MILLIMETERS  
TOLERANCES: EXCEPT AS NOTED  
MM ANGLE  
X. ± 0.35 X.\* ± 2°  
.X ± 0.30 .X\* ± 1°  
.XX ± 0.25 .XX\* ± 0.5°  
.XXX ± 0.15 .XXX\* ± 0.5°

APPROVALS

DATE

DRAWN OW 9/8/20

CHECKED JL 9/8/20

APPROVED

**ADAM**  
**TECH**  
**INTERCONNECTS**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE  
OPTICAL LC ADAPTERS, APC&PC&MM, 2 PORTS  
SHORT EARS, WITH LC DUST CAP

SIZE X PART NO. OPLX2BNNC1XA REV. A

REF: S00005C SCALE: NTS SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[OPLD2BNNC1PA](#) [OPLA2BNNC1PA](#)