



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## USB Console Interface Module for NetDirector Matrix KVM Switches

MODEL NUMBER: **B062-002-USB**



### Description

Tripp Lite's USB Console Interface Module allows a user to access a B060-Series NetDirector Matrix KVM Switch from as far away as 500 ft. The console (keyboard, monitor and mouse) is connected to the HD15 port and USB port on the unit. The B062-002-USB is then connected to a B060-Series NetDirector Matrix KVM Switch via ordinary CAT5e cable.

The unit also includes a 2-in-1 USB KVM Cable kit for connecting to a local computer/server. Simply use the switch on the front of the box to toggle between PC use and KVM switch use...no need to set up a separate console station.

### Features

- Access a B060-Series NetDirector Matrix KVM switch from up to 500 ft. away
- Built-in KVM Switch for additional PC/server control
- Connects to KVM switch via inexpensive Cat5e patch cables
- Compact, space saving design
- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases

### Highlights

- Needed to connect a console (USB Keyboard, USB Mouse and HD15 Monitor) to a B060-Series NetDirector Matrix KVM Switch via Cat5e cable
- Connect to KVM Switch from up to 500 ft. away
- Module features a built-in KVM Switch for additional PC/server control
- Small footprint design takes up very little space on the desktop
- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases

### System Requirements

- USB keyboard, USB mouse and monitor with a HD15 port
- A B060-Series NetDirector Matrix KVM Switch
- Cat5e/6 cable; up to 500ft

### Package Includes

- 1 USB Console Interface Module with Built-in KVM Switch
- External power supply with NEMA 1-15P Plug (Input: 100-240V, 0.8A, 27-34VA, 50/60Hz Output: DC 5V, 2.6A)
- 2-in-1 USB KVM Cable Kit

## Specifications

OVERVIEW	
UPC Code	037332133137
AC Adapter	Input: 100-240V, 0.8A, 27-34VA, 50/60Hz Output: DC 5V, 2.6A



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Technology	Cat5/5e; USB; VGA/SVGA
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	21.59 x 9.40 x 26.92
Shipping Dimensions (hwd / in.)	8.50 x 3.70 x 10.60
Shipping Weight (kg)	1.04
Shipping Weight (lbs.)	2.30
<b>CONNECTIONS</b>	
Computer/Server Ports	1
Included KVM Cable (Equipment Side) - Connector 1	HD15 (Male)
Included KVM Cable (Equipment Side) - Connector 2	USB A (Male)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B062-002-USB](#)