

4-Port Keystone Single-Gang Faceplate, White, TAA

MODEL NUMBER: **N080-104**



Clean, simple wall-mount faceplate for terminating in-wall audio/video, voice and Ethernet cable lines. Works with any type of keystone jack, including those used in Cat5e/6/6a, USB, HDMI, DisplayPort and RCA applications.

Description

The N080-104 4-Port Single-Gang Universal Keystone Wallplate provides a clean and simple method for connecting audio/video, voice and Ethernet cable lines at the wall. Any type of keystone jack, such as those used in Cat5e/6/6a, USB, HDMI, DisplayPort and RCA applications, snaps easily into the cutouts for quick cable connection. White color blends elegantly into any home or office décor for a sleek, professional installation. Made from high-impact polycarbonate. Fits any mid-sized or standard single-gang box. Includes two mounting screws for easy installation. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

Connects Audio/Video, Voice and Ethernet Cable Lines at the Wall

- Works with any type of keystone jack, including those used in Cat5e/6/6a, USB, HDMI, DisplayPort and RCA applications
- Mounting hardware included

Durable Construction

- Made from high-impact polycarbonate
- White color blends into any home or office décor
- Fits any mid-sized or standard single-gang box

TAA Compliant

- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Compatible with any type of keystone jack
- White color blends into any home or office décor
- High-impact polycarbonate construction
- Fits any mid-sized or standard single-gang box
- Includes mounting screws

Package Includes

- N080-104 4-Port Single-Gang Universal Keystone Wallplate, White
- Mounting hardware



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

| OVERVIEW | |
|-------------------------------------|--|
| UPC Code | 037332195562 |
| Technology | Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); USB 3.0 (SuperSpeed); HDBaseT; HDMI; FireWire; DisplayPort |
| PHYSICAL | |
| Color | White |
| Shipping Dimensions (hwd / cm) | 16.99 x 10.01 x 1.27 |
| Shipping Dimensions (hwd / in.) | 6.69 x 3.94 x 0.50 |
| Shipping Weight (kg) | 0.05 |
| Shipping Weight (lbs.) | 0.10 |
| CONNECTIONS | |
| Ports | 4 |
| Side A - Connector 1 | KEYSTONE JACK CUTOUT |
| Side B - Connector 1 | KEYSTONE JACK CUTOUT |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N080-104](#)