

Smart IP Access - Extend KVM control over IP

MODEL NUMBER: 0SU51068



Description

Add remote IP access to existing servers

Preserve your investment

Built-in Serial control

128-bit SSL security

Features

- Adds remote KVM control servers, computers, and KVM switches
- Features two ports for remote control of serial devices
- Features dual NIC ports for network redundancy and security
- Able to utilize a standard 56Kbps analog modem connection, while allowing adaptive and configurable bandwidth consumption when accessed via LAN
- SNMP traps for monitoring Smart IP Access events and operation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Adds remote KVM control servers, computers, and KVM switches
- Features two ports for remote control of serial devices
- Features dual NIC ports for network redundancy and security
- Able to utilize a standard 56Kbps analog modem connection, while allowing adaptive and configurable bandwidth consumption when accessed via LAN
- SNMP traps for monitoring Smart IP Access events and operation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Operating System

- Host Computer - DOS, Windows, Novell, Linux
- Client Computer - Windows with IE 6.0 or higher

Resolution

- Host Computer: Up to 1600 x 1200 @ 85Hz
- Client Computer:
Recommended - client computer resolution should be higher than resolution on the host computer

Package Includes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Smart Access Unit
- KVM Cable Kit
- RS232 Cable
- Rackmount Kit

Specifications

OVERVIEW	
UPC Code	654518206241
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	7.11 x 17.27 x 8.89
Shipping Dimensions (hwd / in.)	2.80 x 6.80 x 3.50
Shipping Weight (kg)	0.41
Shipping Weight (lbs.)	0.90
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C/ -40 to 158 F
Relative Humidity	80% Non-Condensing
Operating Temperature	0 to 40 C / 32 to 104 F
CONNECTIONS	
PC/Server Connections	VGA; PS/2
FEATURES & SPECIFICATIONS	
Number of Users	1
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[0SU51068](#)