

RF Digital Coax Gold Audio Cable (RCA M/M), 6 ft. (1.83 m)

MODEL NUMBER: **A060-006**



Description

Tripp Lite's premium Digital Coax Audio Cable provides a clean, accurate sound, as well as noise and interference elimination that can compromise your listening pleasure. This 6-ft. (1.83 m) cable is specifically designed for digital devices, providing better sonic accuracy and more detailed, natural sound. This cable features a 75 ohm coaxial conductor made of 99.99% pure copper, and precision machined, 6-cut Gold RCA connectors, that resist corrosion.

Features

- Superb audio clarity with more natural sounding mid-range
- Premium-grade, 99.99% pure copper conductors
- Nitrogen-injected dielectric material delivers better high frequencies and a more realistic stereo image
- 6-cut, RCA connectors, with split-tip center pin, ensure a precise connection
- 24kt gold plating resists corrosion and provides increased durability
- Integrated color coded connectors
- Abrasion resistant flexible PVC jacket

Specifications

OVERVIEW	
UPC Code	037332121875
Product Type	Passive
Technology	Stereo Audio
PHYSICAL	

Highlights

- Superior audio quality for movies with Dolby Digital and DTS Surround-Sound
- Double shielded construction for maximum EMI/RFI protection
- Excellent noise isolation with 100% aluminum mylar foil/braid shield
- Silver Plated center conductor for best High Frequency response

System Requirements

- Home Theater or Stereo equipment with RCA digital audio connectors

Package Includes

- 6-ft. (1.83 m) RF Digital Coax Gold Audio Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.21
CONNECTIONS	
Side A - Connector 1	RCA (MALE)
Side B - Connector 1	RCA (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[A060-006](#)