



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.triplite.com

## RG6/U Quad-Shield CMR-Rated Coaxial Cable, Black, 1000 ft. (304.8 m)

MODEL NUMBER: A224-01K-BK



Premium coaxial cabling designed for high-frequency indoor/outdoor applications, such as television antennas, digital cable and satellite transmissions, and video surveillance systems.

### Features

#### Coaxial Cabling for High-Frequency Indoor/Outdoor Applications

- Ideal for television antennas, digital cable and satellite transmissions, and video surveillance systems
- Black 75-ohm cable tested to 3 GHz
- Lower attenuation than RG59 cable for longer distances

#### Premium Construction for Superior Performance

- 18 AWG copper-clad steel center conductor
- Quad foil and braid shielding for error-free transmission
- Flame-retardant CMR-rated PVC jacket
- Meets UL1655, UL13, UL444 and RoHS standards

### Highlights

- Lower attenuation than RG59 cable for longer distances
- 18 AWG copper-clad steel center conductor
- Quad foil and braid shielding for error-free transmission
- Flame-retardant CMR-rated PVC jacket
- Meets UL1655, UL13, UL444 and RoHS standards

### Package Includes

- A224-01K-BK RG6/U Quad-Shield CMR-Rated Coaxial Cable, Black, 1000-ft. (304.8 m)

## Specifications

OVERVIEW	
UPC Code	037332196408
Technology	Coax; RG59/RG6
PHYSICAL	
Color	Black
Cable Jacket Rating	CMR



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (ft.)	1000
Cable Length (m)	304.8
Shipping Dimensions (hwd / cm)	24.00 x 53.01 x 53.01
Shipping Dimensions (hwd / in.)	9.45 x 20.87 x 20.87
Shipping Weight (kg)	15.88
Shipping Weight (lbs.)	35.00
<b>CONNECTIONS</b>	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
<b>SPECIAL FEATURES</b>	
Snagless Connector	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[A224-01K-BK](#)