


Duplex Multimode 62.5/125 Fiber Patch Cable (LC/ST), 5M (16 ft.)

MODEL NUMBER: N318-05M



Highlights

- Manufactured from 62.5/125 duplex (zipcord) fiber
- Ideal for LAN applications
- Glass fiber composition

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with ST/LC connectors

Package Includes

- 5-meter duplex MMF LC/ST 62.5/125 fiber cable

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 5-meter/Connectors: 2 ST/LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

OVERVIEW	
UPC Code	037332134998
Technology	Multimode
Optical Mode	OM1
PHYSICAL	
Cable Jacket Color	Orange
Clad Diameter	125 micron
Core Diameter	62.5 micron
Number of Fibers	2



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	16.4
Cable Length (m)	5
Cable Length (in.)	196.9
Shipping Dimensions (hwd / cm)	24.13 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.50 x 7.00 x 0.50
Shipping Weight (kg)	0.04
Shipping Weight (lbs.)	0.08
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	ST DUPLEX (MALE)
SPECIAL FEATURES	
Push/Pull Tabs	No
STANDARDS & COMPLIANCE	
Certifications	ROHS
Approvals	FDDI and OFNR rated
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N318-05M](#)