

Multi-Device Charging Station, 16 AC Outlets, Chromebooks and Laptops, White

MODEL NUMBER: **CSC16ACW**



Locking steel cabinet provides AC charging, secure storage and cord management for up to 16 Chromebooks and laptops. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Description

The CSC16ACW 16-Device AC Charging Station Cabinet provides AC charging, secure storage and cord management for up to 16 Chromebooks and laptops. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

16 AC outlets provide convenient charging for Chromebooks and laptops with a screen size up to 15 inches. Their AC adapters plug into the cabinet's 16 NEMA 5-15R outlets as needed, up to 1,440 total watts. The CSC16ACW also charges tablets and other USB devices through their power adapters. A built-in circuit breaker protects against overloads. The 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets to help you place the cart in a convenient location.

The cabinet promotes comprehensive device protection with steel construction and a white powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering, and flow-through ventilation helps prevent overheating.

The cabinet also encourages clutter-reducing organization of devices and cabling. AC outlets, power adapters and cords store out of sight. A toolless trim panel permits quick service access.

The cabinet is easy to configure. The cabinet It ships fully assembled. and supports mounting to a wall, desk, table, counter or floor. The front doors open 180 degrees for improved device and service access. Rear-panel slots support optional wall-mount installation, and removable dividers accommodate thicker devices. You can also convert it the cabinet to a mobile cart with Tripp Lite's optional CSHANDLEKIT2 (sold separately), and roll it where needed.

Features

Convenient Charging Charges 16 Chromebooks and laptops up to 15 in. screen size
 Device power adapters plug into NEMA 5-15R outlets (up to 1,440 watts total)
 Also charges tablets and other USB devices through their power adapters
 Built-in circuit breaker protects against overloads
 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets

Comprehensive Protection Sturdy steel construction and powder-coated finish promote long-term durability
 Doors lock with included keys to help prevent device theft, damage or tampering
 3-point locking mechanism latches doors at top, middle and bottom
 Built-in hasp and user-supplied padlock can replace or supplement built-in lock
 Rear ports accommodate user-supplied bicycle cable or chain lock
 Flow-through ventilation helps prevent devices from overheating
 Protective shelf specially coated to avoid device scratches and scuffs
 Cord access ports with rubber grommets protect against abrasions
 Solid top work surface helps avoid accidental drips and spills that could damage devices

Clutter-Reducing Organization AC outlets, power adapters and cords store out of sight
 Toolless trim

Highlights

- Charges 16 Chromebooks and laptops up to 15 in. screen size
- Secures devices in locking, vented steel cabinet with cart option
- Protective shelf with removable dividers and cord management
- Supports mounting to wall, desk, table, counter or floor
- Ships fully assembled for quick, easy installation

Package Includes

- CSC16ACW 16-Device AC Charging Station Cabinet, White
- (2) Keys
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

panel permits quick access to AC adapters and cords
Shelf includes charging cord access ports for each device
Staggered outlets fit power adapters without blocking adjacent outlets
Flexible Configuration Ships fully assembled for quick, easy installation
Supports mounting to wall, desk, table, counter or floor
Split front doors open 180 degrees for improved device and service access
Removable dividers accommodate thicker devices like battery chargers
Converts to mobile cart with optional CSHANDLEKIT2 (sold separately)

Specifications

OVERVIEW	
UPC Code	037332194817
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Functions	Charge; Secure
Device Compatibility	Chromebook; Laptop
Device Slots	16
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	120
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	16
Charging Method	AC
Charging Port Type	NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(16) 12A
Overcharge Protection	No
Charging Amps per Port	12A
PHYSICAL	
Color	White
Antimicrobial Coating	No
Charging Station Form Factor	Stationary Cabinet



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Material of Construction	Steel
Shipping Dimensions (hwd / cm)	62.31 x 59.99 x 85.50
Shipping Dimensions (hwd / in.)	24.53 x 23.62 x 33.66
Shipping Weight (kg)	47.17
Shipping Weight (lbs.)	104.00
Slot Dimensions (hwd / in.)	10.6 x 1.5 x 15.4
Slot Dimensions (hwd / mm)	268.1 x 38.2 x 390.5
Unit Dimensions (cm)	47.54 x 77.04 x 54.86
Unit Dimensions (hwd / cm)	47.54 x 77.04 x 54.86
Unit Dimensions (hwd / in.)	18.8 x 30.3 x 21.6
Unit Weight (kg)	34.10
Unit Weight (lbs.)	75.17
Number of Shelves	1
SPECIAL FEATURES	
Cord Management	Yes
EMI/RFI Line Noise Protection	No
Locking	Yes
Lock Type	Key
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
STANDARDS & COMPLIANCE	
Certifications	Tested to EIA-310-E, FCC & IEC Class B, UL 1363 (Power Component)
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[CSC16ACW](#)