

## Easy Pull Type-A Connectors - (M/M set of VGA with Audio)

MODEL NUMBER: **EZA-VGAAM-2**



### Highlights

- SVGA / 3.5mm Stereo Connector Kit, Male to Male
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

### Package Includes

- 2 x HD15 Male/3.5mm Stereo Male, 1 ft. pigtails

### Description

Easy Pull Connector Kit includes: 2 x HD15 Male w/stereo 3.5mm plug, 1 ft. pigtails. Video support up to 1600 x 1200. Use with either PVC or Plenum trunk cables.

### Features

- Easy Pull, 2 x HD15 Male & 2 x 3.5mm Stereo, 1 ft. pigtails
- Eliminates the need to field terminate VGA connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35 ft., 50 ft. and 100 ft. PVC lengths, and 35 ft. and 50 ft. Plenum jackets
- Support resolutions up to 1600 x 1200

## Specifications

| OVERVIEW           |                        |
|--------------------|------------------------|
| UPC Code           | 037332141958           |
| Product Type       | Passive                |
| Technology         | VGA/SVGA; Stereo Audio |
| PHYSICAL           |                        |
| Color              | Black; Green           |
| Cable Length (ft.) | 1                      |
| Cable Length (m)   | 0.3                    |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                           |
|-------------------------------------|---------------------------|
| Shipping Dimensions (hwd / cm)      | 1.27 x 14.99 x 21.34      |
| Shipping Dimensions (hwd / in.)     | 0.50 x 5.90 x 8.40        |
| Shipping Weight (kg)                | 0.14                      |
| Shipping Weight (lbs.)              | 0.30                      |
| <b>CONNECTIONS</b>                  |                           |
| Side A - Connector 1                | HD15 (MALE)               |
| Side A - Connector 2                | 3.5MM (MALE)              |
| Side A - Connector 3                | DIN 14 PIN (MALE)         |
| Side B - Connector 1                | HD15 (MALE)               |
| Side B - Connector 2                | 3.5MM (MALE)              |
| Side B - Connector 3                | DIN 14 PIN (MALE)         |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[EZA-VGAAM-2](#)