



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## USB Sync/Charge Cable with Apple 30-Pin Dock Connector, White, 3 ft. (0.91 m)

MODEL NUMBER: **M110-003-WH**



Charge and sync your Apple 30-pin iPhone, iPad or iPod using the USB port on your computer.

### Description

The M110-003-WH USB Sync/Charge Cable connects your iPhone, iPad or iPod with the USB port on any computer, so you can charge your Apple device and transfer data. This 3-ft. (0.91 m) cable is MFi-certified for use with the latest generation of iPhone, iPad and iPod devices.

### Features

**Syncs and Charges Your Apple 30-Pin Electronic Devices** MFi-certified for use with the latest generation of iPhone, iPad and iPod devices)

**Compact and Convenient to Use** Connects your 30-pin iPhone, iPad or iPod device and the USB port on your computer or wall charger Works with all computers

### Highlights

- Features an Apple-compatible 30-pin plug and a USB-A plug
- Works with any computer
- MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod
- Compatible with all Apple devices with 30-pin connectors

### System Requirements

- USB-equipped computer or charger
- iPhone, iPad, iPad mini, iPad mini 2, iPad mini 3, iPad mini 4, iPad Air, iPad Air 2, iPad Pro 12.9 inch, iPad Pro 10.5 inch, iPad Pro 9.7 inch and iPod Touch devices with Lightning port

### Package Includes

- M110-003-WH USB Sync/Charge Cable with Apple 30-Pin Dock Connector

## Specifications

OVERVIEW	
UPC Code	037332190062
Technology	Apple® 30-Pin Dock; USB
PHYSICAL	
Color	White
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.8mm
Cable Length (ft.)	3
Cable Length (m)	1



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Material of Construction	PVC
Shipping Dimensions (hwd / cm)	13.21 x 2.29 x 6.60
Shipping Dimensions (hwd / in.)	5.20 x 0.90 x 2.60
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	0% to 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	30 PIN APPLE (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to MFI, CA65, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[M110-003-WH](#)