

## DisplayPort 1.2 to DVI Compact Adapter Video Converter (M/F)

MODEL NUMBER: **P134-000-DVI-V2**



### Description

Tripp Lite's P134-000-DVI-V2 DisplayPort v1.2 to DVI Adapter Converter allows you to connect a computer with a DisplayPort connection to a DVI monitor. Displayport v1.2 doubles the previous version bandwidth of 8.64 Gbps to 17.28 Gbps in High Bit Rate (HBR2) mode, which allows increased resolutions, higher refresh rates, and greater color depth. Fully molded one piece design ensures longer life. The P134-000-DVI-V2 is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port, which allows HDMI and DVI signals to be passed through. Check the documentation for your DisplayPort source for compatibility.

### Features

- Connect a DVI monitor to a computer with a DisplayPort output
- DisplayPort v1.2 to DVI Adapter Converter (DisplayPort-Male to DVI-I Female)
- Supports DVI single-link computer video resolutions up to 1920 x 1080 (1080p)
- 17.28 Gbps bandwidth
- Fully molded one piece design
- Plug and Play; no drivers or software required
- Requires that the connected computer has a DP++ (DisplayPort ++) port, which allows HDMI and DVI signals to be passed through; check the documentation for your DisplayPort source for compatibility.

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332187550 |

### Highlights

- Connect a DVI monitor to a computer with a DisplayPort output
- DisplayPort v1.2 to DVI Adapter Converter (DisplayPort-Male to DVI-I Female)
- Plug-and-play convenience; no drivers or software needed
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode mode

### Package Includes

- DisplayPort 1.2 to DVI Compact Adapter Converter (DP-Male to DVI-I Female)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                         |
|-------------------------------------|-------------------------|
| Technology                          | DVI; DisplayPort        |
| <b>PHYSICAL</b>                     |                         |
| Color                               | Black                   |
| Shipping Dimensions (hwd / cm)      | 14.99 x 9.91 x 1.27     |
| Shipping Dimensions (hwd / in.)     | 5.90 x 3.90 x 0.50      |
| Shipping Weight (kg)                | 0.02                    |
| Shipping Weight (lbs.)              | 0.04                    |
| <b>CONNECTIONS</b>                  |                         |
| Side A - Connector 1                | DISPLAYPORT (MALE)      |
| Side B - Connector 1                | DVI-I (FEMALE)          |
| <b>WARRANTY</b>                     |                         |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P134-000-DVI-V2](#)