

## Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Video Converter Adapter, 4K 30Hz HDMI, DP1.2, Black, 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-HDV-4K



All-in-one converter/adapter connects your Mini DisplayPort-enabled laptop or tablet to a VGA, DVI or HDMI display without the need to carry separate adapters. Ideal for trade shows, classrooms and lecture halls.

### Features

#### Connects Your Mini DisplayPort Laptop or Tablet to a VGA, DVI or HDMI Display

- Recommended for trade shows, classrooms, lecture halls and other presentations
- DVI port supports video resolutions up to 1920 x 1080 (1080p)
- HD15 port supports video resolutions up to 1920 x 1200, including 1080p
- HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 36-bit Deep Color (12 bits per channel)
- Ideal for Chromebooks, MacBooks, Microsoft Surface and laptops equipped with Mini DisplayPort or Thunderbolt 1 & 2 ports

### Plug-and-Play Convenience

- No software, drivers or external power supply required
- Small enough to stow in laptop bag or briefcase
- Passive adapter requires connected computer to have DP++ port

## Specifications

### Highlights

- Separate DVI, HD15 and HDMI female connectors
- HDMI port supports UHD 4K x 2K @ 24/30 Hz video resolutions
- Passive adapter requires connected computer to have DP++ port
- Plug and play—no software, drivers or power supply needed
- Small size for easy carrying in laptop bag or briefcase

### System Requirements

- Passive adapter requires the connected computer to have a DP++ ( Displayport ++ ) port

### Package Includes

- P137-06N-HDV-4K Mini DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual

### OVERVIEW

UPC Code

037332190833



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Technology	DVI; HDMI; VGA/SVGA; DisplayPort
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	10.01 x 14.00 x 2.31
Shipping Dimensions (hwd / in.)	3.94 x 5.51 x 0.91
Shipping Weight (kg)	0.07
Shipping Weight (lbs.)	0.16
<b>CONNECTIONS</b>	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P137-06N-HDV-4K](#)