

## Power Extension Cord, NEMA L5-30P to NEMA L5-20R Extension Cord with Breaker - 20A, 120V, 10 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P043-002



L5-30P to L5-20R extension cord with breaker transforms a NEMA L5-30R wall outlet into a NEMA L5-20R outlet.

### Features

**Heavy-Duty Extension Cable Connects Devices That Require a Heavy-Gauge Connection** This heavy-duty extension cord with breaker features 10 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It comes with a built-in metal 20-amp breaker box, which allows you to transform a NEMA L5-30R wall outlet into a NEMA L5-20R outlet. It is also a recommended replacement or upgrade of a standard power cord provided by the device's manufacturer. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

**Locking Connectors Help Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. Locking connectors on each end help you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

### Highlights

- Built-in 20A breaker allows easy transition to L5-20R outlet with no electrician needed
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
- Thick 10 AWG wire gauge manages high power levels required for larger equipment
- Locking connectors maintain secure link to avoid loss of power and costly downtime

### Applications

- Connect PDUs and UPS systems to a power outlet up to 2-ft. (0.61 m) away in your office or workspace
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source in a rack
- Transform a NEMA L5-30R outlet into a NEMA L5-20R outlet with no electrician needed
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P043-002 L5-30P to L5-20R Extension Cord with Breaker, 2-ft. (0.61 m), Black

## Specifications



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

OVERVIEW	
UPC Code	037332142306
Device Compatibility	UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	120
PHYSICAL	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	10
Wire Gauge (OD - mm <sup>2</sup> )	5.26
Cable Length (ft.)	2
Cable Length (m)	0.6
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	48.01 x 29.97 x 1.27
Shipping Dimensions (hwd / in.)	18.90 x 11.80 x 0.50
Shipping Weight (kg)	0.50
Shipping Weight (lbs.)	1.10
CONNECTIONS	
Side A - Connector 1	NEMA L5-30P
Side B - Connector 1	NEMA L5-20R
SPECIAL FEATURES	
High Voltage	No
Locking Plug	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P043-002](#)