

HDMI to DVI Adapter Cable (M/M), 16 ft. (4.9 m)

MODEL NUMBER: **P566-016**



Highlights

- Premium Double Shielded Digital Video Cable
- Gold plated connectors provide low-loss
- Bandwidth up to 5Gbps

Package Includes

- 16-ft. (4.88 m) HDMI to DVI Gold Digital Video Cable - HDMI-M/DVI-M

Creates a pure digital connection between a DVI-enabled computer and a HDMI-enabled display or TV

Description

Tripp Lite's 16-ft. (4.88 m) DVI - HDMI (High Definition Multimedia Interface) cable allows interconnection between digital display devices, such as DTV's (Digital Television), Plasma displays, LCD TV's, and projectors, to Digital source devices, such as Digital Set-Top boxes, DVD/DVD-R players, and AV receivers. HDMI DTV's will display video received from existing DVI-equipped products, and DVI-equipped TVs will display video from HDMI sources. HDMI technology uses a much more compact and user-friendly connector than the existing DVI connector. The HDMI specification handles higher-bandwidth, uncompressed video, and multi-channel digital audio, all in one neat cable solution. (DVI-HDMI cable supports video digital only).

Features

- Creates a pure digital connection between a DVI-enabled computer and a HDMI-enabled display or TV
- Gold plated connectors provide optimal signal transfer
- Premium Double-Shielded HDMI compliant cable protects against outside noise (EMI/RFI)
- Impedance matched twisted pair construction reduces cross-talk and interference

Specifications

OVERVIEW	
UPC Code	037332122902
Product Type	Passive
Technology	DVI; HDMI
PHYSICAL	
Color	Black
Cable Length (ft.)	16



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	4.9
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.70
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P566-016](#)