

# 40 Pin F IDE to Serial ATA (SATA) Drive Adapter Converter

MODEL NUMBER: **P936-000**



## Description

Tripp Lites P936-000, Serial ATA (SATA) to IDE converter, allows a standard parallel ATA hard disk drive, CD-ROM, CD-RW, DVD ROM, DVD + RW, etc, to be used with Serial ATA Controller cards or motherboards with Serial ATA ports, and meets the specification of Serial ATA 1.0 interface. Simply plug the 40-pin side of the adapter into the IDE drive 40-pin connector, and attach power and SATA cables to the appropriate connections...no software to load.

## Features

- Easily connect IDE/ATA Drives to a SATA Controller
- Compliance with Serial ATA Gen 1.0.
- Master/slave device emulation support.
- Supports PIO mode 0~4.
- Supports Ultra DMA mode 0~7.
- Supports UDMA data transfer rates of up to 150MBps
- Supports ATAPI Packet command set.
- Supports 48-bit LBA addressing.
- Supports additional ATA command for serial ATA SCR access.
- Serial ATA power save mode supported
- Serial ATA BIST operation.
- Supports hot-plugging

## Specifications

### Highlights

- Convert existing IDE Drives to a SATA Controller
- Serial ATA (SATA) Data & Power Cable Included

### System Requirements

- Supports any operating system when a PC with available IDE hard disk and SATA controller are used

### Package Includes

- Serial ATA to IDE Converter x 1
- Serial ATA Cable x 1
- Power supply cable x 1
- User's Manual x 1

### OVERVIEW

UPC Code

037332152053



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Technology	SATA/eSATA; Ribbon/Internal
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	17.78 x 13.97 x 3.18
Shipping Dimensions (hwd / in.)	7.00 x 5.50 x 1.25
Shipping Weight (kg)	0.08
Shipping Weight (lbs.)	0.17
<b>CONNECTIONS</b>	
Side A - Connector 1	IDE 40PIN SOCKET
Side B - Connector 1	7 PIN SATA (MALE)
Side B - Connector 2	LP4 (FEMALE)
Side B - Connector 3	LP4 (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P936-000](#)