




Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS Replacement Battery Cartridge for select Tripp Lite SmartOnline Tower UPS

MODEL NUMBER: RBC24-SUTWR



Highlights

- Tripp Lite-certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leakproof construction
- Maintenance free
- Wide operating temperature range

Package Includes

- One pre-assembled battery pack consisting of 2 12V batteries

Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications, and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. See Tripp Lite's UPS replacement battery web page to confirm compatibility and quantity required. COMPATIBLE WITH TRIPP LITE MODELS SU750XL, SU1000XL. NOT COMPATIBLE WITH SUINT1000XL MODELS (see the Tripp Lite RBC selector guide to verify the correct battery set for your UPS)

Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

Specifications

OVERVIEW	
UPC Code	037332131430
BATTERY	
DC System Voltage (VDC)	24
Included Battery Set	Contains (2) 12V 9AH sealed lead acid batteries
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	15.29 x 25.30 x 30.00
Shipping Dimensions (hwd / in.)	6.02 x 9.96 x 11.81
Shipping Weight (kg)	6.49
Shipping Weight (lbs.)	14.30
Unit Dimensions (hwd / cm)	19.7 x 15.9 x 7
Unit Dimensions (hwd / in.)	7.75 x 6.25 x 2.75
Unit Weight (kg)	5.58
Unit Weight (lbs.)	12.3
ENVIRONMENTAL	
Operating Elevation (ft.)	0-10,000 ft
Storage Elevation (ft.)	0-10,000 ft
Operating Elevation (m)	0-3000 m
Storage Elevation (m)	0 - 3,000 m
WARRANTY	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[RBC24-SUTWR](#)