

Universal Reversible USB 2.0 Cable (Reversible A to Reversible A M/M), 6-ft.

MODEL NUMBER: UR020-006



Reversible USB connector plugs in any direction

Description

Easily connect USB devices without fumbling with the connector. Tripp Lite Reversible USB cables have connectors that work in either direction, so you don't have to look to see which is right-side-up anymore.

Notes:

1. USB Male-to-Male cable is not a standard USB cable configuration, and is only used in rare instances where a peripheral or patch bay employs a USB A-Female connection, in place of USB B-type port.
2. This cable will not work as a PC-to-PC connection. File sharing between computers requires special, software-driven file transfer cables, such as Tripp Lite U233-006-MP-R.

Features

- USB 2.0 Male-to-Male, with Universal / Reversible connectors
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold contacts and molded ends provide a lifetime of use

Specifications

OVERVIEW	
UPC Code	037332179395
Technology	USB 2.0 (High Speed); USB (all versions)
INPUT	

Highlights

- 6ft, USB 2.0, Male-to-Male
- Universal, Reversible connector allows plugging in any direction

System Requirements

- Computer with USB A-Female port
- USB device or Patch port with USB A-Female port

Package Includes

- 6ft, USB 2.0, Male-to-Male
Universal / Reversible Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Wire Gauge (AWG)	28/24
Shipping Dimensions (hwd / in.)	7.000 x 9.000 x 0.500
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.1400
Shipping Weight (kg)	0.06
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	REVERSIBLE USB A (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[UR020-006](#)