

Full Motion Dual Desk Clamp for 13 to 27" monitors and laptops up to 15"

MODEL NUMBER: **DDR1327NBMSC**



Description

Tripp Lite's VESA-compliant DDR1327NBMSC Flex Arm Dual Desk Clamp frees up valuable space in your workstation. The unique flexible design offers an exceptional range of motion. Dual swivel arms are independently height adjustable to allow complete flexibility to position your monitor and laptop independently. The DDR1327NBMSC offers complete flexibility to position devices for your maximum comfort and visual preference. It features convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 27-inch flat-panel displays and laptops up to 15". Its durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any decor. It comes with all necessary mounting hardware, and supports monitors up to 22 lbs. and laptops up to 11 lbs.

Features

- VESA-compliant Flex Arm Dual Flat-Screen Desk Clamp frees up valuable space in your workstation in providing a single solution for you monitor and laptop
- Unique flexible design with swivel arms that are independently height adjustable offers an exceptional range of motion
- Convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 27-inch flat-panel displays and laptops up to 15 inches
- Durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any decor
- Includes all necessary mounting hardware to support monitors up to 22 lbs. and laptops up to 11 lbs.

Specifications

PHYSICAL	
Mounting Location	Desk Clamp
Unit Dimensions (hwd / in.)	12.52 x 33.86 x 4.45

Highlights

- Increases available desk/table space in office workstation applications
- Dual mounts fit most flat-panel displays from 13" to 27" and laptops up to 15"
- Convenient one-touch display adjustment for easy view optimization and improved ergonomics
- Wide range of motion with -80° to +90° tilt, 180° swivel and 360° rotation capability
- Each mount supports monitors up to 22 lbs. and laptops up to 11 lbs.

Package Includes

- DDR1327NBMSC Dual Full-Motion Flex Arm Desk Clamp for 13" to 27" Flat-Screen Displays and Laptops up to 15"
- Mounting Hardware
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / cm)	31.80 x 86.0 x 11.30
Unit Weight (lbs.)	7.53
Unit Weight (kg)	3.42
Material of Construction	Steel
Color	Black
Monitor Display Size (in.)	13 - 27
Monitor Display Size (cm)	33.02 - 68.58
Laptop Display Size (in.)	5 - 15
Laptop Display Size (cm)	12.7 - 38.1
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-80/+90 Tilt; 180 swivel; 360 rotate
Maximum Weight Capacity (lbs.)	22
Maximum Weight Capacity (kg)	9.98
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DDR1327NBMSC](#)