

USB 2.0 Adapter Cable, USB-C to USB Micro-B (M/F), 6-in. (15.24 cm)

MODEL NUMBER: **U040-06N-MIC-F**



Convert the USB Type-C (USB-C) port on your device, tablet, laptop, ultrabook, or computer to a USB Micro-B Female port

Features

- 6-in. USB Type-C (USB-C) Male to USB Micro-B Female adapter cable
- Converts the USB Type-C port on your tablet, laptop, ultrabook, or computer to a USB Micro-B port, allowing for Micro-B devices to sync and charge
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 30AWG Data Pair / 24AWG Power Pair

Specifications

OVERVIEW	
UPC Code	037332189226
Technology	USB 2.0 (High Speed); USB
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	3.0MM
Cable Jacket Rating	VW-1

Highlights

- Connect devices with a USB Micro-B port to the USB Type-C (USB-C) port on your tablet, laptop, ultrabook or computers
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in

System Requirements

- A device with a Micro-B connector
- A tablet, laptop, ultrabook or computer with an available USB Type-C (USB-C) port

Package Includes

- USB 2.0 Hi-Speed Adapter Cable, USB Type-C (USB-C) Male to USB Micro-B Female, 6-in.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10% to 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	MICRO-USB B (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U040-06N-MIC-F](#)