

## FC to ST 62.5/125 Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: **T020-001-ST62**



Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an ST connector. Ideal for cable installers or anyone else working in telecom or LAN environments.

### Description

The T020-001-ST62 FC to ST 62.5/125 Adapter converts a native FC fiber female port on the Tripp Lite T020-001-PSF Multi-Function Optical Fiber Cable Tester to an ST female port for 62.5/125 multimode cable testing. "62.5/125" is clearly labeled on the unit to differentiate the T020-001-ST62 from other adapters. Included dust caps keep the connectors clean when not in use.

### Features

#### Converts Cable Tester's FC Connector to an ST Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 62.5/125 multimode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with T020-001-PSF Multi-Function Optical Fiber Cable Tester

## Specifications

OVERVIEW	
UPC Code	037332197689
Technology	Multimode
PHYSICAL	

### Highlights

- Converts native FC jack to an ST female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 62.5/125 multimode cable testing
- Included dust caps keep connectors clean
- For use with T020-001-PSF Optical Fiber Cable Tester

### System Requirements

- Tripp Lite T020-001-PSF Multi-Function Optical Fiber Cable Tester

### Package Includes

- T020-001-ST62 FC to ST 62.5/125 Adapter



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Color	Silver
Clad Diameter	125
Core Diameter	62.5
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.04
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[T020-001-ST62](#)