

## Virtual 7.1-Channel USB External Sound Card

MODEL NUMBER: **U237-001**



Adds external microphone, speaker and/or headphone ports, as well as volume and mute controls, to your computer or laptop via USB port. An inexpensive replacement for damaged sound cards or audio connectors.

### Description

The U237-001 Virtual 7.1-Channel USB External Sound Card plugs into your computer or laptop's USB port to provide easy-to-access audio-in and audio-out ports. A convenient, inexpensive replacement for a damaged sound card or audio connectors, the U237-001 lets you plug a microphone, speakers and/or headphones into its 3.5 mm audio jacks and enjoy rich, vibrant sound. By installing the Xear™ 3D Virtual 7.1-Channel Surround Sound software (included), you'll be able to customize the audio settings. In addition to the two audio ports, the U237-001 features volume controls, microphone and speaker muting buttons, and LEDs that indicate audio status, activity and microphone/speaker mute. It's plug-and-play, with the USB audio driver automatically installing upon connection to a USB port. Compatible with Windows® 2000™ and later, Mac OS X® and Linux. Xear 3D software compatible with Windows XP, 7 and 8™.

### Features

**Adds an External Sound Card to Your Computer's USB Port** Dual 3.5 mm audio jacks for connecting microphone, speakers and/or headphones  
 Inexpensive replacement for damaged sound card or audio connectors  
 Easy-access volume controls  
 Microphone/speaker muting buttons  
 LEDs indicate status, activity and mute

**Xear 3D Virtual 7.1-Channel Surround Sound Software** Customizable audio settings  
 Supports 3D and virtual 7.1-channel surround sound  
 Preset sound effects with 10-band equalizer  
 Software compatible with Windows XP, 7 and 8

**Easy to Use** Plug and play—no external power supply required  
 USB driver automatically installs upon connection  
 Unit compatible with Windows 2000 and later, Mac OS X and Linux

### Highlights

- Customizable audio settings via included CD software
- Supports 3D and virtual 7.1-channel surround sound
- LEDs indicate status, activity and speaker/microphone mute
- Plug and play—no external power supply required
- Compatible with Windows, Mac and Linux

### System Requirements

- Available USB-A port
- 3.5 mm stereo speakers, headphones and/or microphone
- Windows 2000 and later, Mac OS X or Linux
- Windows XP, 7 and 8 (Xear 3D software)

### Package Includes

- U237-001 USB External Sound Card
- Xear 3D software CD
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332192745
Technology	Stereo Audio; USB; USB 2.0 (High Speed)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

AUDIO	
Audio Specification	7.1 Surround Sound
INPUT	
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Speaker/Mic Mute), Green (Active)
PHYSICAL	
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	14.73 x 5.51 x 10.67
Shipping Dimensions (hwd / in.)	5.80 x 2.17 x 4.20
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.55 x 2.2 x 1
Unit Packaging Type	Clamshell
Unit Weight (kg)	0.01
Unit Weight (lbs.)	0.02
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F ( -10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
Power Consumption (Watts)	0.5
CONNECTIONS	
Ports	2
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) 3.5MM (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH, WEEE
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U237-001](#)