





## Dual Flat-Panel Rail Wall Mount for 10" to 24"

### TVs and Monitors

MODEL NUMBER: **DMR1024X2**



Low-profile rail mount hangs 2 flat-panel televisions, monitors or other displays on the wall.

Recommended for video walls, menu boards and other displays in restaurants, bars, airports, hotels, offices and boardrooms.

### Description

The VESA-compliant DMR1024X2 Dual Flat-Panel Rail Wall Mount allows you to mount two flat-panel televisions, monitors or other displays on the wall in either portrait or landscape mode. Recommended for video walls, menu boards and other display applications in restaurants, bars, airports, hotels, offices and boardrooms, the low-profile mount fits most flat-panel displays from 10 to 24 inches.

Dual displays attach to VESA mounts that can slide closer or further apart along the rail for optimal viewing. The rail is concealed behind the displays for a sleek, professional appearance. Included cable guides attach to the rail to keep power cords out of the way.

Durable steel construction supports up to 18 lbs (8.2 kgs) per VESA mount. Mounting hardware is included. Conforms to VESA-compliant displays with either of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

### Features

#### Mounts 2 Televisions or Monitors to the Wall

- Fits most flat-panel TVs, monitors and other displays from 10 to 24 in.
- Ideal for video walls, menu boards and other display applications in restaurants, bars, airports, hotels, offices and boardrooms
- Designed for portrait or landscape mounting

#### Innovative Rail Design

- VESA mounts adjust independently along rail

### Highlights

- Fits most flat-panel displays from 10 to 24 in.
- Designed for portrait or landscape mounting
- VESA mounts adjust independently along rail
- Durable steel construction
- Supports up to 18 lbs (8.2 kgs) per VESA mount

### Package Includes

- Wall rail
- (2) VESA mounts
- (8) M4 x 12 screws
- (8) M4 x 30 screws
- (8) Spacers
- (3) Cable guides
- (5) Anchor bolts
- (5) Concrete anchors
- (5) Washers
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- Rail conceals behind displays for sleek, professional appearance
- Cables attach to rail to prevent tangles and clutter
- Adjustable mounting rails match up with off-center wall studs
- Wall-mounting hardware included

#### Durable Steel Construction

- Supports up to 18 lbs (8.2 kgs) per VESA mount

#### VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm and 100 x 100 mm

## Specifications

OVERVIEW	
UPC Code	037332202826
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black; Silver
VESA Pattern (mm)	75x75; 100x100
Degrees of Motion	-15/+15 Tilt; 20 Swivel; 360 Rotate
Material of Construction	Steel
Maximum Screen Size (cm)	60.96
Maximum Screen Size (in.)	24
Maximum Weight Capacity (kg)	8
Maximum Weight Capacity (lbs.)	18
Min/Max Arm Extension (cm)	7.62
Min/Max Arm Extension (in.)	3
Minimum Screen Size (in.)	10
Minimum Screen Size (cm)	25.4
Motion	Fixed
Mounting Location	Wall
Number of Displays	2
Shipping Dimensions (hwd / cm)	12.80 x 129.49 x 6.20
Shipping Dimensions (hwd / in.)	5.04 x 50.98 x 2.44
Shipping Weight (kg)	2.94



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Weight (lbs.)	6.49
Unit Dimensions (hwd / cm)	12 x 127 x 6
Unit Dimensions (hwd / in.)	4.72 x 50 x 3.35
Unit Weight (kg)	2.30
Unit Weight (lbs.)	5.08
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
<b>SPECIAL FEATURES</b>	
Cord Management	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DMR1024X2](#)