

## USB 3.0 SuperSpeed to SATA III Adapter for 2.5 in. to 3.5 in. SATA Hard Drives

MODEL NUMBER: **U338-000-SATA**



Format new hard drives, or salvage data off old drives

### Description

Tripp Lite's U338-000-SATA USB 3.0 SuperSpeed to SATA III Adapter allows connection to a Serial ATA Hard drive (2.5" / 3.5" ). Configure hard drives without having to install them first, or, pull data from a crashed computer hard drive to a new computer. The unit features a 22-Pin SATA Data + Power connector, and USB 3.0 Micro-B connector . Works with any 2.5 in. to 3.5 in. SATA Hard Drive. The U338-000-SATA is compatible with Windows (up to 10) and Mac, and can be connected to older USB generation computers ( 2.0 and 1.1, at slower speeds )

### Features

- USB 3.0 and below compliant
- SATA III ( 6Gbps ) and below compliant
- Supports Plug-and-Play...No Drivers or Software needed
- Supports LBA-48 bit ( Logical Block Addressing )
- Supports USB Mass Storage Class Bulk-Only Transport
- 22-Pin SATA Data + Power connector
- Compatible with 2.5" / 3.5" SATA Hard drives
- Supports drives up to 4TB
- Compatible with Windows (up to 10), Mac, Linux

## Specifications

### OVERVIEW

### Highlights

- SuperSpeed (5Gbps) / Hi-Speed (480 Mbps) / Full-Speed (12 Mbps) Compliant
- SATA III (6Gbps) / SATA Gen2i (3Gbps) / Gen1i (1.5Gbps) Compliant
- For 2.5 in. to 3.5 in. SATA Hard Drives
- Supports drives up to 4TB
- Compatible with Windows (up to 10), MAC, LINUX

### System Requirements

- Computer with USB 3.0 port ( 2.0 and 1.1 compatible, but at slower transfer speeds )
- SATA 2.5" or 3.5" Hard Drive

### Package Includes

- U338-000-SATA USB 3.0 SuperSpeed to SATA III Adapter
- USB 3.0 Micro-B Cable, 2.5 ft.
- External Power Supply with NEMA 1-15P Plug ( Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A )



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

UPC Code	037332182135
AC Adapter	Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A
Technology	USB 3.0 (SuperSpeed); SATA/eSATA; USB
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	7.62 x 8.13 x 12.70
Shipping Dimensions (hwd / in.)	3.00 x 3.20 x 5.00
Shipping Weight (kg)	0.25
Shipping Weight (lbs.)	0.56
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-20C to +85C
Storage Temperature Range	-20C to +70C
<b>CONNECTIONS</b>	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U338-000-SATA](#)