

+/-144VDC External Battery Pack for Tripp Lite 208V SUT-Series UPS

MODEL NUMBER: BP288VEBP



External battery pack provides extended runtime for compatible 3-phase 208V Tripp Lite UPS systems.

Features

+/-144VDC External Battery Pack Gives Your Compatible UPS System Extended RuntimeThe BP288VEBP is compatible only with Tripp Lite's 3-phase 208V SUT20K, SUT30K, SUT40K, SUT60K and other UPS systems that specify the use of this battery pack. Not only does it provide extended runtime, but it can also be daisy-chained to additional external battery packs for even longer extended-run operation. The three-pole input/output terminal blocks allow safe, simple hardwire installation, as well as internal disconnect for battery isolation.

Rugged Steel Construction Designed to Last in Busy IT ApplicationsThe steel cabinet features front and rear doors that provide easy access to the recyclable internal batteries and input/output terminal blocks. A 250A circuit breaker protects your equipment from dangerous overcurrent or overloads, while 63A fuses guard each battery string. Pre-installed rolling casters allow you to move the cabinet smoothly to its intended destination. Use the adjustable levelers for secure deployment on a stable surface.

One-Year WarrantyThe BP288VEBP is backed by a one-year warranty, ensuring reliability and performance.

Highlights

- Connects to expandable 208V Tripp Lite SUT-Series UPS systems for extended runtime
- Supports daisy-chaining to additional battery packs for even longer runtime
- Steel cabinet has front/rear doors for easy access to recyclable internal batteries
- 250A DC breaker protects equipment from potentially hazardous overcurrent
- Pre-installed metal casters allow you to smoothly roll the unit to its destination

Applications

- Extend the runtime of your compatible Tripp Lite UPS system to maintain operation during all power conditions
- Daisy-chain to additional battery packs to provide even longer extended-run operation for backing up essential equipment

System Requirements

- Tripp Lite SUT20K, SUT30K, SUT40K, SUT60K or other UPS system specifying compatibility with this external battery pack

Package Includes

- BP288VEBP +/-144VDC External Battery Pack for Tripp Lite 208V SUT-Series UPS
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332204110
INPUT	
Input Phase	3-Phase
BATTERY	
Expandable Battery Runtime	Multiple battery packs can be daisy-chained to the UPS for extended runtime
Expandable Runtime	Yes
DC System Voltage (VDC)	+/- 144VDC
UPS Connection	Hardwire (contractor supplies wiring - see Owner's Manual for gauge recommendations and complete installation instructions)
PHYSICAL	
External Battery Pack Form Factor	Tower
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	76.50 x 68.00 x 95.00
Shipping Dimensions (hwd / in.)	30.12 x 26.77 x 37.40
Shipping Weight (kg)	395.08
Shipping Weight (lbs.)	871.00
Unit Dimensions (hwd / cm)	199.9 x 101.6 x 74.9
Unit Dimensions (hwd / in.)	23.5 x 30.08 x 33.58
Unit Weight (kg)	350.00
Unit Weight (lbs.)	771.62
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[BP288VEBP](#)