


## 36V External Battery Pack for Select Tripp Lite UPS Systems, 2U Rack/Tower

MODEL NUMBER: **BP36V27-2US**



External battery pack provides extended runtime for compatible 36V DC Tripp Lite UPS systems.

### Features

**External Battery Pack Gives Your Compatible Tripp Lite UPS System Extended Runtime**The BP36V27-2US is compatible only with select 36V DC Tripp Lite UPS systems that specify the use of this battery pack. Not only does it provide extended runtime, but it can also be daisy-chained using its rear connector to additional external battery packs for even longer extended-run operation. Heavy-gauge cabling with high-current two-point DC connector is included for simple installation. Optional-use rear-panel battery detection jacks automatically configure host UPS systems supporting this feature for one or more external battery packs.

**Versatile Installation Options Allow You to Place the Battery Where Most Needed**The steel housing supports mounting in 2U of space in EIA-standard 19-inch racks using the included 4-post rack-mounting brackets. The BP36V27-2US is also compatible with Tripp Lite's 2-9USTAND for upright tower configuration, 2POSTRMKITWM for 2-post racks or wall installation and UPDHDEARKIT for 2-point front-rail rack installation without rear supports (all accessories sold separately).

**2-Year Warranty**The BP36V27-2US is backed by a 2-year warranty, ensuring reliability and performance.

### Highlights

- Connects to expandable 36V DC Tripp Lite UPS systems for extended runtime
- Daisy-chain connector supports additional battery packs for even longer runtime
- Optional-use detection jacks auto-configure select UPS systems for quicker setup
- Mounts in 2U of space in 19 in. rack using included 4-post installation hardware
- Supports 2-post rack, 2-point rail, wall or tower installation with optional accessories

### Applications

- Extend the runtime of your compatible Tripp Lite UPS system
- Daisy-chain to additional battery packs to provide even longer extended-run operation

### System Requirements

- Compatible with  
 SMART1000RMXL2U,  
 SMART1200XLHG,  
 SMART1500RMXL2UA,  
 SMART1500RMXLN,  
 SMART1500XL,  
 SMX1200XLHG,  
 SMX1500XLRT2U and other  
 Tripp Lite UPS systems that specify the use of this battery pack

### Package Includes

- BP36V27-2US 36V External



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Battery Pack w/attached DC  
cabling

- Rack-mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332181770
INPUT	
Input Phase	Single-Phase
BATTERY	
DC System Voltage (VDC)	36
UPS Connection	Attached 18in. / 457mm 6AWG cable with 50A gray 2-point DC connector
Typical Battery Lifespan	3-6 years typical (North America)
PHYSICAL	
External Battery Pack Form Factor	Rack/Tower
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> ); 2-4 post front rail rackmount ( <a href="http://www.tripplite.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT">UPSHDEARKIT</a> ); 4 post rackmount short-depth ( <a href="http://www.tripplite.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4POSTRAILKITWM</a> ); Tower ( <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> ); Wallmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> );
Material of Construction	Steel
Minimum Required Rack Depth (cm)	73.91
Minimum Required Rack Depth (inches)	29.1
Optional Mounting Accessory Notes	Optional <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> ; enables upright tower UPS placement; <a href="http://www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> ; enables wall-mount and 2-post rackmount installation; <a href="http://www.tripplite.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4POSTRAILKITWM</a> ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); <a href="http://www.tripplite.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT">UPSHDEARKIT</a> ; enables installation in 2 or 4-post racks using front vertical rails only, without rear support



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Rack Height	2U
Shipping Dimensions (hwd / cm)	24.13 x 67.31 x 72.39
Shipping Dimensions (hwd / in.)	9.50 x 26.50 x 28.50
Shipping Weight (kg)	47.63
Shipping Weight (lbs.)	105.00
Unit Dimensions (hwd / cm)	8.71 x 44 x 57.4
Unit Dimensions (hwd / in.)	3.43 x 17.32 x 22.6
Unit Weight (kg)	31.26
Unit Weight (lbs.)	68.91
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[BP36V27-2US](#)