

Compact HDMI to VGA Adapter Video Converter with Audio (M/F)

MODEL NUMBER: **P131-000-A**



Compact HDMI to VGA converter delivers digital audio and 1080p video from the HDMI port on your laptop, notebook or PC to your existing VGA TV, monitor or projector.

Description

The P131-000-A HDMI to VGA Adapter with Audio (M/F) helps you transmit digital audio and 1080p video from your laptop, Chromebook, MacBook or PC to a VGA-enabled television, monitor or projector. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen, or streaming video for digital signage in crystal-clear 1080p.

This HDMI to VGA adapter supports video resolutions up to 1920 x 1200 (including 1080p HD) at 60 Hz. Just insert the HDMI male converter into the HDMI source, and connect a VGA cable (sold separately) between the VGA female port and the VGA display. To share stereo audio, connect a 3.5 mm audio cable (sold separately) between the adapter's audio jack and the audio jack on the VGA display, A/V receiver or speakers.

The molded one-piece unit is so compact that it fits in the palm of your hand, making it easy to carry in your backpack or laptop bag for quick connection anywhere. No software, drivers or external power supply is required. If additional power is needed, connect the converter's USB Micro-B port to a USB charger or a USB-A port on the source device.

Features

Connects a VGA Display to Your HDMI Device

- Ideal for giving video presentations, editing multiple documents, or streaming video for digital signage
- Supports video resolutions up to 1920 x 1200 (including 1080p HD) @ 60 Hz
- 3.5 mm jack included for sharing stereo audio from HDMI source
- Active I2C communication for more efficient data transfer

Plug-and-Play Operation

- No software or external power supply required
- Molded 1-piece unit fits in the palm of your hand
- Easy to carry in a pocket, purse or laptop bag
- Bus-powered via HDMI; USB Micro-B port included in case more power is needed

Highlights

- Supports video resolutions up to 1920 x 1200 (including 1080p HD) @ 60 Hz
- Fits in the palm of your hand for easy carrying anywhere
- 3.5 mm jack included for sharing stereo audio from HDMI source
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- Source device with HDMI output
- Display device with VGA input
- Although external power is not required in most installations, a USB Micro-B port is provided in the event that it is. If so, the 5V 500mA provided by a standard USB 2.0 port will be sufficient to support functionality.

Package Includes

- P131-000-A HDMI to VGA Adapter with Audio (M/F)
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332205780
Technology	HDMI; Stereo Audio; VGA/SVGA
PHYSICAL	
Color	Black
Cable Length (ft.)	0
Cable Length (in.)	0
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.01
Shipping Weight (lbs.)	0.03
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	3.5MM (FEMALE); HD15 (FEMALE); MICRO-USB B (FEMALE)
FEATURES & SPECIFICATIONS	
HDCP Specification	1.4
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P131-000-A](#)