

HDMI to VGA Active Adapter Video Converter with Audio (F/M)

MODEL NUMBER: P131-000-A-DISP



Active converter connects a VGA-enabled television or monitor to the HDMI port on your PC, MacBook, Chromebook, laptop or tablet.

Features

Now You Can Watch Video from Your HDMI Computer on a VGA Display This HDMI to VGA adapter helps you transmit video through your computer's HDMI port to a VGA-enabled television or monitor. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen, or streaming video for digital signage in crystal-clear 1080p. It also allows you to keep using your VGA display without the expense of replacing it.

Transmits Crystal-Clear 1080p Video and Stereo Audio To send high-definition video to a VGA television or monitor, connect the adapter directly to the display's VGA port, and connect an HDMI cable (sold separately) between the adapter's HDMI port and the source device. The adapter supports video resolutions up to 1920 x 1200 (including 1080p) at 60 Hz. Connect the included audio cable between the adapter's audio port and the audio jack on your monitor, A/V receiver or speakers to receive stereo sound.

Ready to Use Right Out of the Package The molded one-piece unit is so compact that it fits in the palm of your hand, making it easy to carry in your backpack or laptop bag for quick connection anywhere. No software, drivers or external power supply is required. If additional power is needed, use the included USB cable to connect the adapter's USB Micro-B port to a USB charger or a USB-A port on the source device.

Highlights

- Recommended for video presentations or streaming 1080p video for digital signage
- Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Included 3.5 mm audio cable carries stereo sound to monitor, receiver or speakers
- Molded one-piece converter fits easily in your backpack or laptop bag
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Play video from your HDMI computer on a large-screen VGA television
- Write and edit multiple documents on a bigger monitor
- Stream 1080p video for digital signage at a trade show
- Give a video presentation from your laptop at a meeting, training session or conference

System Requirements

- Source device with HDMI output
- Display device with VGA input

Package Includes

- P131-000-A-DISP HDMI to VGA Adapter with Audio (F/M)
- USB Micro-B to USB-A cable, 1 ft.
- 3.5 mm stereo audio cable, 1 ft.
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332231208
Product Type	Video Adapter
Device Compatibility	Computer; Laptop; Monitor/HDTV
Technology	HDMI; Stereo Audio; VGA/SVGA

VIDEO	
Supported Resolutions	1920x1200
Max Supported Video Resolution	1920 x 1200 (1080p)
Max Supported Color Depth	8-bit
3D Video Supported	No
AUDIO	
Audio Specification	2 Channel Audio
INPUT	
Bus Powered	Yes
Product Length (in.)	2.46
Product Length (ft.)	0.20
POWER	
Power Consumption (Watts)	1.26
PHYSICAL	
Color	Black
Material of Construction	ABS
Cable Length (ft.)	0
Cable Length (m)	0.00
Cable Length (in.)	0
Rackmountable	No
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	1.330 x 2.460 x 0.370
Unit Dimensions (hwd / cm)	3.38 x 6.25 x 0.94
Unit Weight (lbs.)	0.10
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	10% to 90% RH, Non-Condensing
COMMUNICATIONS	

EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	No
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	3.5MM (FEMALE); HDMI (FEMALE); MICRO-USB B (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
HDCP Specification	1.4
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; EN 55035
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P131-000-A-DISP](#)