

## DisplayPort to DVI Cable Adapter, Converter for DP-M to DVI-I-F, 6-in. (15.24 cm), 50 Pack

MODEL NUMBER: **P134-000-50BK**



Passive adapters connect your computer or tablet's DisplayPort™ to the DVI input on a monitor, projector or television. Source devices must have DisplayPort++ (DP++) for HDMI/DVI pass-through.

### Features

#### Send High-Definition DisplayPort Video Signals to a DVI Display

- Connects DisplayPort computer or tablet to DVI-enabled monitor, projector or TV
- Recommended for digital signage or presentations in a classroom or conference room
- Male DisplayPort and female DVI-I dual-link connectors
- Bulk pack includes 50 Tripp Lite P134-000 DisplayPort to DVI converters

### Vibrant Video Quality

- Supports DVI-D single-link video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Passive adapter requires source device to have DP++ compatibility for HDMI/DVI signal pass-through

### Superior Materials for Superior Performance

- Foil and braid shielding helps protect against EMI/RFI line noise that can distort or destroy data
- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking

### Convenient to Use Anywhere

- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

## Specifications

### Highlights

- 50-piece bulk pack of P134-000 DisplayPort to DVI adapters
- Supports DVI-D single-link video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1080p
- Premium foil and braid shielding helps protect against EMI/RFI noise
- Plug and play—no software, drivers or power supply needed

### System Requirements

- Source device with DisplayPort output
- Display device with DVI input
- Source must have DP++ port for HDMI/DVI pass-through
- Not for use with MST hubs

### Package Includes

- (50) P134-000 DisplayPort to DVI Cable Adapters (M/F), 6 in.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

OVERVIEW	
UPC Code	037332205506
Technology	DVI; DisplayPort
PHYSICAL	
Color	Black
Cable Length (ft.)	0.5
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	16.08 x 30.18 x 17.14
Shipping Dimensions (hwd / in.)	6.33 x 11.88 x 6.75
Shipping Weight (kg)	2.72
Shipping Weight (lbs.)	6.00
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P134-000-50BK](#)