

DisplayPort to DVI Dual-Link Active Adapter Video Converter (M/F), 6-in. (15.24 cm)

MODEL NUMBER: **P134-06N-DVI-DL**



Converts any DisplayPort video signal for display on a DVI-I single-link or dual-link monitor, projector or television.

Features

Send High-Definition DisplayPort Video Signals to a DVI Display Connects DisplayPort computer to DVI-I dual-link monitor, projector or TV Active converter works with all DisplayPort signals Ideal for displaying video on large monitor or digital sign
Vibrant, Superior Video Quality Supports DVI dual-link video resolutions up to 2560 x 1600 Supports DVI single-link video resolutions up to 1920 x 1080 (1080p) Supports 24-bit Deep Color (8 bits per channel) Converts Multi-Mode (DP++) and Single-Mode DisplayPort output Works with graphics cards that don't output DP++ signals, such as AMD Eyefinity
Superior Materials for Superior Performance Gold-plated connectors and contacts for excellent conductivity Integral strain relief for long life Plug-and-play—no software, drivers or power supply necessary Fits easily into briefcase, backpack or laptop bag

Highlights

- Active converter works with all DisplayPort signals
- Supports DVI dual-link video resolutions up to 2560 x 1600
- Supports DVI single-link video resolutions up to 1920 x 1080
- Converts Multi-Mode (DP++) and Single-Mode DisplayPort output
- Plug and play—no software, drivers or power supply needed

System Requirements

- Computer with DisplayPort and USB port
- Display with DVI output
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P134-06N-DVI-V2

Package Includes

- P134-06N-DVI-DL DisplayPort to DVI Dual-Link Active Converter (M/F), 6 in.

Specifications

OVERVIEW	
UPC Code	037332198716
Technology	DVI; DisplayPort
PHYSICAL	
Color	Silver
Cable Length (ft.)	0.5
Cable Length (in.)	6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	3.30 x 8.89 x 15.75
Shipping Dimensions (hwd / in.)	1.30 x 3.50 x 6.20
Shipping Weight (kg)	0.16
Shipping Weight (lbs.)	0.35
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	DVI-I DUAL LINK (FEMALE) (WIRED TO DVI-D DUAL LINK)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P134-06N-DVI-DL](#)