



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Keyspan Mini DisplayPort to HDMI Active Adapter/Video Converter (M/F) - 4K 60 Hz, DP 1.2, HDCP 2.2, White, 6 in.

MODEL NUMBER: P137-06N-H2V2



Converts Mini DisplayPort (mDP) 1.2 audio and 4K x 2K video for display on an HDMI monitor, projector or television.

Features

Sends Mini DisplayPort 1.2 Audio/Video to an HDMI Display Connects PC or Mac's mDP or Thunderbolt 1 & 2 output to HDMI-enabled monitor, projector or TV. Ideal for displaying video on large monitor or digital sign.

Vibrant Video Quality Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160) as specified in HDMI 2.0. Supports audio and HDCP 2.2. Converts both Single-Mode and Dual-Mode DisplayPort output. Works with graphics cards that don't output DP++ signals.

Superior Materials for Superior Performance Nickel-plated connectors and gold-plated contacts for excellent conductivity. Integral strain relief for long life. Plug-and-play—no software, drivers or power supply necessary. Fits easily into briefcase, backpack or laptop bag.

Highlights

- Complies with mDP and Thunderbolt 1 & 2 ports on PCs and Macs
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports audio and HDCP 2.2
- Converts both Single-Mode and Dual-Mode mDP output

System Requirements

- PC or Mac with mDP or Thunderbolt 1 & 2 output
- Display with HDMI input
- Both display and source must support 4K x 2K @ 60 Hz to display 4K x 2K video
- Audio supported as long as source does. Check source manual for compatibility.

Package Includes

- P137-06N-H2V2 Keyspan Mini DisplayPort 1.2 to HDMI Active Adapter (M/F), 6 in.

Specifications

OVERVIEW	
UPC Code	037332200341
Technology	HDMI; DisplayPort
PHYSICAL	
Color	White
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P137-06N-H2V2](#)