

## UPS Replacement Battery Cartridge for Tripp Lite SUINT1000LCD2U UPS System, 24V

MODEL NUMBER: RBC24S



UPS backup battery replacement breathes new life into a Tripp Lite UPS system suffering from expired or weak internal batteries.

### Features

#### UPS Replacement Battery Cartridge for Tripp Lite SUINT1000LCD2U UPS System

This UPS backup battery replacement is carefully screened and certified to meet or exceed original specifications. The leakproof, no-maintenance RBC24S comes pre-assembled and pre-wired as two 12V batteries for quick and easy installation in your SUINT1000LCD2U. It functions within a wide range of operating temperatures. A sensor automatically informs the UPS that the battery has been replaced, so the UPS can reset the battery age. Reusable packaging allows you to easily send expired batteries to a recycling center.

### Highlights

- Replacement battery backup for Tripp Lite SUINT1000LCD2U UPS system
- Carefully screened and certified to restore UPS runtime to original specs
- Leakproof internal battery requires no regular maintenance
- Ships fully assembled and ready for immediate installation to prevent downtime
- Auto-detection sensor allows UPS to reset internal battery age

### Applications

- Replace the aging or expired internal battery in your Tripp Lite SUINT1000LCD2U UPS system

### System Requirements

- Compatible with Tripp Lite SUINT1000LCD2U UPS system

### Package Includes

- RBC24S UPS Battery Replacement (pre-assembled battery pack with two 12V batteries)

## Specifications

OVERVIEW	
UPC Code	037332239372
BATTERY	
DC System Voltage (VDC)	24
Included Battery Set	Contains (2) 12V 9AH sealed lead acid batteries



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Typical Battery Lifespan	3 to 5 years typical, depending on UPS operating conditions
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	5.51 x 12.00 x 8.86
Shipping Weight (kg)	6.50
Unit Dimensions (hwd / cm)	6.71 x 15.11 x 20.09
Unit Dimensions (hwd / in.)	2.64 x 5.95 x 7.91
Unit Weight (kg)	6.50
Unit Weight (lbs.)	14.33
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[RBC24S](#)