


Cantilevered Steel Rack Shelf - 1U, Vented, Integrated Cable Rings, 14.2 in. Deep, Holds up to 50 lbs (22.2 kgs)

MODEL NUMBER: **SRWSHELF4P1U**



Robust vented shelf mounts in 1U of rack space to secure a power strip or other device and save space in your data center or server room.

Features

1U Vented Cantilevered Rack Shelf Secures Non-Rack Equipment in Your Data Center This SmartRack® cantilevered shelf supports monitors, power strips, PDUs, wireless access points and other network and IT equipment not typically stored in a rack. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRWSHELF4P1U has a maximum load capacity of 50 lbs (22.2 kgs). Its adjustable rails mount easily into 1U of space in EIA-standard 19-inch enclosures and open frame racks using included hardware.

Custom Setup Maximizes Rack Space and Saves Desk or Floor Space in a Busy Office The steel shelf is 14.2 inches deep. The surface is perforated with square mounting holes that accept cage nuts, giving you multiple options for installing equipment for convenient access. The vented surface also augments proper airflow to keep your equipment cool and functioning at its peak. Built-in flexible cable rings help you manage and secure cabling and cut down on intrusive cord clutter.

Highlights

- Cantilevered 1U rack shelf secures non-rack equipment like WAPs and power strips
- Heavy-duty cold-rolled steel construction with maximum load capacity of 50 lbs (22.2 kgs)
- Perforated with square mounting holes for custom device installations using cage nuts
- Vented design maximizes airflow to protect equipment against excessive heat
- Integrated cable management rings eliminate messy and bothersome cable clutter

Applications

- Store a power strip, wireless access point, small PDU or other mission-critical non-rack devices inside a cabinet or open frame rack

Package Includes

- SRWSHELF4P1U Cantilevered Steel Rack Shelf, 1U
- Rack-mounting hardware

Specifications

OVERVIEW	
UPC Code	037332225016
PHYSICAL	
Shipping Dimensions (hwd / cm)	7.40 x 51.50 x 51.50
Shipping Dimensions (hwd / in.)	2.91 x 20.27 x 20.27
Shipping Weight (kg)	5.20



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	11.46
Unit Dimensions (hwd / cm)	4.318 x 48.006 x 45.2882
Unit Dimensions (hwd / in.)	1.700 x 18.900 x 17.830
Unit Weight (kg)	5.00
Unit Weight (lbs.)	11.020
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRWSHELF4P1U](#)