




**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## SmartOnline Step-Down Isolation Transformer, 208V to 120V, 5kVA, 5kW, 2U Rack-Mount, TAA

MODEL NUMBER: **SU5000XFMR2UTAA**



5kVA 5kW transformer converts UPS, utility, generator or other 208V input to 120V for powering low-voltage AC components.

### Features

**208V to 120V Isolation Transformer Converts High-Voltage Input to Low-Voltage Output** The 5kVA 5kW SU5000XFMR2UTAA SmartOnline® Step-Down Isolation Transformer converts your UPS, utility or generator's 208V high-voltage input to 120V low-voltage output. It features 12 NEMA 5-15/20R outlets for connecting equipment with common NEMA 5-15P and NEMA 5-20P plugs. Four resettable 20A circuit breakers protect your low-voltage equipment against overload conditions. One NEMA L6-30R outlet supports high-voltage output. The 5kVA transformer's 10-ft. (3.05 m) power cord with 208V 30A input connects to a NEMA L6-30R outlet.

**Versatile Installation Options** Hardware is included for mounting this 208V to 120V isolation transformer in 2U of space in an EIA-standard 19-inch 4-post rack with a maximum depth requirement of 20.75 inches. Use the optional 2POSTRMKITWM for 2-post rack mounting or the optional 2-9USTAND for mounting in an upright tower position (both accessories sold separately).

**TAA-Compliant UPS for GSA Schedule Purchases** The SU5000XFMR2UTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

**2-Year Warranty and Environmentally Responsible Design** The SU5000XFMR2UTAA comes with a 2-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

### Highlights

- Converts high-voltage AC output into low voltage for powering low-voltage equipment
- 12 NEMA 5-15/20R outlets for connecting components with 5-15P or 5-20P plugs
- Resettable circuit breakers protect connected equipment from hazardous overloads
- NEMA L6-30R outlet accepts high-voltage equipment
- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

- Connecting low-voltage (120V) equipment to a high-voltage (208V) AC power source

### Package Includes

- SU5000XFMR2UTAA SmartOnline Step-Down Isolation Transformer
- Rack-mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332214645
INPUT	
Nominal Input Voltage(s) Supported	208V AC
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Recommended Electrical Service	208V 30A
Maximum Input Amps	24
Input Connection Type	NEMA L6-30P
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output (VA)	5000
Output (Watts)	5000
Output Receptacles	(12) 5-15/20R; (1) L6-30R
Output Nominal Voltage	120/208V AC
Overload Protection	Includes 4 built-in 20A circuit breakers. Each breaker protects 3 5-15/20R outlets each.
<b>PHYSICAL</b>	
Form Factors Supported	Rack/Tower (2U)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	21.84 x 50.55 x 59.44
Shipping Dimensions (hwd / in.)	8.60 x 19.90 x 23.40
Shipping Weight (kg)	33.79
Shipping Weight (lbs.)	74.50
Unit Dimensions (hwd / cm)	8.9 x 44.5 x 52.7
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 20.75
Unit Weight (kg)	25.85
Unit Weight (lbs.)	57
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% (non-condensing)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	TAA Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SU5000XFMR2UTAA](#)