



Cable Ladder, 2 Sections - SRCABLETRAY or SRLADDERATTACH Required, 10 x 1.5 ft. (3 x 0.3 m)

MODEL NUMBER: **SRCABLELADDER18**



Provides roof-mounted cable routing for Tripp Lite SmartRack® enclosures, allowing cable bundles to span aisles or spaces between racks.

Features

Eliminate Cable Stress by Organizing Cabling Outside Your Enclosure or Open Frame Rack The SmartRack SRCABLELADDER18 mounts to the top of your rack enclosure or open frame rack for overhead cable routing. Install it either parallel or perpendicular to the rack for clean, organized cable routing across an aisle or within a row. Each SRCABLELADDER measures 10-ft. (3.05 m) long and 1.5-ft. (0.45 m) wide for safe cable bundling. It requires the use of Tripp Lite's SRCABLETRAY (for enclosures) or SRLADDERATTACH (for open frame racks) for installation (both accessories sold separately). An included grounding stud allows tie-in to the rack and facility ground. The SRCABLELADDER18 ships in two 5-ft. (1.52 m) sections for convenient storage and assembly.

Highlights

- Cuts cable clutter by routing cable bundles overhead in your data center
- Allows cables to span aisles or spaces between racks in the same row
- Measures 10-ft. (3.05 m) long and 1.5-ft. (0.45 m) wide for organized cable bundling
- Arrives boxed in dual 5-ft. (1.52 m) sections for easy shipping, storage and assembly
- Works in tandem with Tripp Lite SRCABLETRAY or SRLADDERATTACH (sold separately)

Applications

- Neatly bundle cable across an aisle or within a row of bayed racks in your data center

System Requirements

- SRCABLETRAY (rack enclosures) or SRLADDERATTACH (open frame racks)

Package Includes

- (2) Ladder sections
- (4) Assembly brackets
- (8) Clevis pins
- (8) Cotter pins
- (2) Ground brackets
- (2) M6 hex bolts
- (3) Ground cables, 2-ft. (0.61 m)
- (4) Ladder clamps
- (4) M6 lock washers
- (2) M6 hex nuts



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- (2) M10 x 60 mm carriage bolts
- (2) M10 lock washers
- (2) M10 hex nuts
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332214614
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	8.51 x 48.01 x 152.70
Shipping Dimensions (hwd / in.)	3.35 x 18.90 x 60.12
Shipping Weight (kg)	9.78
Shipping Weight (lbs.)	21.56
Unit Dimensions (hwd / cm)	3.81 x 45.72 x 299.72
Unit Dimensions (hwd / in.)	1.5 x 18 x 118
Unit Weight (kg)	8.16
Unit Weight (lbs.)	18
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tripp Lite:

[SRCABLELADDER18](#)